

PRODUCT INFORMATION

**L  
LA**



**Intended Use**

For mounting heights up to 16' requiring low to medium light levels. Ideal for light-duty areas, utility, storage rooms or retail.

**Construction**

Solid-top reflector or 8% uplight is available. Sturdy combination reflector and channel cover secured by captive quarter-turn latch for easy access to wireway. Combination end plate/channel connector supplied with each fixture. High-gloss backed

white enamel finish. Reflector is painted after fabrication.

For replacement reflectors, see page 95. For wireguards and mounting accessories, see page 93.

**Electrical**

Ballast: Thermally protected, resetting, Class P, HPF, non-PCB, UL Listed, CSA Certified ballast is standard. Sound rating depends on lamp/ballast combination.

Wiring and electrical: AWM, TFN or THHN wire

used throughout, rated for required temperatures.

Available in tandem wired lengths. Accepts plug-ins for one, two or three primary circuits.

Ballast disconnect provided standard where required to comply with U.S. and Canadian electrical codes.

**Installation**

For unit or row installations, surface or suspended mounting.

**Listings**

UL Listed. CUL Listed or CSA Certified to Canadian standards. NOM Certified – optional.

ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

**Example:** L 2 32 MVOLT GEB10IS


Series <sup>1,2</sup>	Number of lamps	Lamp type	Voltage	Ballast configuration	Ballast	Options
L Solid reflector	1	17 17W T8 (24")	<b>MVOLT</b>	<b>(blank)</b> 1- and/or 2-lamp ballasts per Lithonia Lighting standards	<b>GEB10IS</b> T8 electronic ballast, instant start	EL14 Emergency battery pack
LA 8% uplight	2	20 20W T12 (24") <sup>1</sup>	347 <sup>3</sup>	<b>1/4</b> One 4-lamp ballast	<b>GEB10RS</b> T8 electronic ballast, programmed rapid start	PLF_ Plug-in wiring; specify 1, 2 or 3 branch circuits and hot wires (A=black, B=red C=blue, AB or AC)
	Not included.	<b>32</b> 32W T8 (48")			<b>BINP</b> T8 high-performance ballast, normal ballast factor (.88), instant start	TILW Tandem in-line wiring
		48 38W slimline (48")			<b>BILP</b> T8 high-performance ballast, low ballast factor (.78), instant start	CSA Meets Canadian standards
		48T8HO 44W T8 (48")				NOM Meets Mexican standards
		96T8 59W T8 slimline (96")				
		96T8HO 86W T8 380mA (96")				

ADDITIONAL INFORMATION

For additional product information, visit [www.lithonia.com](http://www.lithonia.com).

SERIES	CONFIGURATIONS					
	LAMPS PER CROSS SECTION	LAMPS PER FIXTURE	LAMP TYPE	WIDTH IN.(CM)	DEPTH IN.(CM)	LENGTH IN.(CM)
L, LA	1	1	17, 20 <sup>1</sup>	12 (30.5)	4 (10.2)	24 (61.0)
L, LA	2	2	17, 20 <sup>1</sup>	12 (30.5)	4 (10.2)	24 (61.0)
L, LA	1	1	32, 48	12 (30.5)	4 (10.2)	48 (121.9)
L, LA	2	2	32, 48, 48T8HO	12 (30.5)	4 (10.2)	48 (121.9)
TL, TLA	1	2	32, 48, 48T8HO	12 (30.5)	4 (10.2)	96 (243.8)
TL, TLA	2	4	32, 48	12 (30.5)	4 (10.2)	96 (243.8)
L, LA	1	1	96T8, 96T8HO	12 (30.5)	4 (10.2)	96 (243.8)
L, LA	2	2	96T8, 96T8HO	12 (30.5)	4 (10.2)	96 (243.8)

Drawings are for dimensional detail only and may not represent actual mechanical configuration. Dimensions are shown in inches (centimeters) unless otherwise noted.



**Notes**

- 1 For tandem double-length unit, add prefix T. Example: TL.
- 2 Consult factory for additional T12 and T12HO configurations.
- 3 Available only with CSA option.