

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

Recessed housing rated IC or Non-IC. For new construction only.
 Approved for all ceiling and wiring types.
 Approved for direct burial in insulation.

CONSTRUCTION

Air-tight standard. Tested to meet current energy codes.
 Aluminum housing with galvanized steel pan.
 Galvanized bar hangers span up to 24" o.c. and feature stepped shank nail and positioning guide with integral T-bar locks. Two locking screws hold fixture in position.
 Galvanized steel junction box with four built-in Romex clamps. Four 1/2" and two 3/4" knockouts with slots for pryout. Rated for through branch wiring. Maximum 4 (2 in, 2 out) No. 12 AWG conductors. Rated for 90° C.
 Ground wire provided.
 Removable J-box doors for easy access.

ELECTRICAL SYSTEM

Durable medium-base porcelain socket with nickel plated copper alloy screw shell and contact.
 Socket clips to top of housing to prevent paint overspray in socket screw shell.
 Socket attaches to reflector to ensure proper and consistent lamp position.
 Thermal protection provided against improper lamp usage.
 120 volt only.

INSTALLATION

Air-tight housing suitable for air-tight installations. Refer to energy codes for proper installations.
 2x8 and 2x6 wood joist or T-bar installation.
 Expandable bar hangers allow for off-center mounting in wood joist or T-bar ceilings. Length of 25-1/2" maximum 13-1/4" minimum or cut to fit 5-1/2" on center joist construction.
 Vertical adjustment of housing allows for flush mounting with ceiling face.
 Suitable for ceilings up to 1-1/2" thick.




LISTING

U.L. Listed to US and Canadian safety standards (see Options).
 Damp location listed.
 See trim selection for wet location listed.

4" Housing

L3

INCANDESCENT
 IC/Non-IC
 New Construction



Specifications

Height: 5-1/4 (13.3)
 Length: 13-1/4 (33.7)
 Width: 12-3/16 (30.9)
 Ceiling Opening: 4 (10.2)

All dimensions are inches (centimeters).

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: L3 R6

L3		
Series	Options	Packaging
L3	(Shipped installed in fixture) PHC Poke-home wire connectors	R6 Resale pack of six U Unit(non-stock)

NOTE:
 See trim summary on reverse side for maximum wattages.

Accessories:
 Order as separate catalog number.
ATK3R6 Airtight trim kit

3 Series 4" Incandescent L3 Full Reflector Trims

Description Catalog number	Maximum wattage Sheet number	Description Catalog number	Maximum wattage Sheet number
-------------------------------	---------------------------------	-------------------------------	---------------------------------

General/Task

Open Narrow Flange

301 White
301A Clear diffuse
301AZ Clear specular anodized
301BLZ Black specular anodized
301BN Brushed nickel
301BZA Antique bronze
301ORB Oil-rubbed bronze

IC  30 R20
35 PAR20

Non IC  50 PAR20
ROPN-250

Baffle Narrow Flange

3B1W White

IC  50 PAR20
50 R20
RBAF-230

Baffle Narrow Flange

3B1 Black
3B1BN Brushed nickel
3B1BZA Antique bronze
3B1ORB Oil-rubbed bronze

IC  35 PAR20
Non IC  50 PAR20
RBAF-230

Baffle Deep Narrow Flange

3B2 Black

Non IC  50 PAR20
50 R20
ROPN-280

Baffle Deep Narrow Flange

3B2W White

IC  30 R20
35 PAR20
Non IC  50 R20
ROPN-280

Accent/Wallwash

Eyeball Narrow Flange

3E1 White
3E1BN Brushed nickel
3E1BZA Antique bronze
3E1ORB Oil-rubbed bronze

IC  50 PAR20
50 R20

RADJ-210

Wallwash Narrow Flange

3W1 White

Non IC  50 R20
50 PAR20
RWLL-170

Pinhole Narrow Flange

3S1 White

IC  35 PAR20
Non IC  50 PAR20
RWLL-200

Wet Location

Wetlite Narrow Flange

3H20 White
3H20BN Brushed nickel
3H20BZA Antique bronze
3H20ORB Oil-rubbed bronze

IC  75 PAR30
Short Neck
RLNS-170

NOTES:

- 1 Maximum wattage listed. Lower wattage lamps may be used.
- 2 Wetlite trim is wet location listed and outdoor rated. All other trims are damp location.