

7100 SERIES FIRE EXTINGUISHER CABINETS

REGULARLY FURNISHED:

BOX- Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish.

DOOR AND FRAME


7107-7129 Series: Steel - Cold rolled steel with recoatable white polyester finish.

7130-7149 Series: Aluminum - Satin finish, clear polyester coated.


7150-7169 Series: Stainless Steel - #304 Stainless Steel with #4 finish.

7170-7189 Series: Brass - Polished finish, clear polyester coated.


Wall mounting and size of cabinet as selected by model number.




RECESSED



TRIMLESS



SEMI-RECESSED



SURFACE

Qty	Model No.				Wall Mounting	Inside Box Dimensions			Overall Frame		Minimum Wall Opening Required			Trim	ADA	For Use With These Extinguishers
	Steel	Aluminum	Stainless Steel	Brass		K	L	M	N	O	W	H	D			
	7107	7137	7157	7177	Recessed	9	18	5	11 ³ / ₄	20 ³ / ₄	10	19	4 ³ / ₄	1/2	Yes	3002 3005, 3005-3 3302 3305 3305-3
	7108	7138	7158	7178	Semi-Recessed	9	18	5	11 ³ / ₄	20 ³ / ₄	10	19	3 ¹ / ₄	2	Yes	
	7109	7139	7159	7179	Surface	11 ¹ / ₂	20 ¹ / ₂	6	-	-	-	-	-	-	No	
	7110	7130	7150	7170	Recessed	9	24	5	11 ³ / ₄	26 ³ / ₄	10	25	4 ³ / ₄	1/2	Yes	
	7112	7132	7152	7172	Semi-Recessed	9	24	5	11 ³ / ₄	26 ³ / ₄	10	25	3 ¹ / ₄	2	Yes	
	7113	7133	7153	7173	Semi-Recessed	9	24	5	11 ³ / ₄	26 ³ / ₄	10	25	2 ¹ / ₄	3	Yes	3006 3010 3306 3310 3405
	7120	7140	7160	7180	Recessed	9	24	5 ³ / ₄	11 ³ / ₄	26 ³ / ₄	10	25	5 ¹ / ₂	1/2	Yes	
	7121	7141	7161	7181	Trimless	9	24	6 ¹ / ₄	12 ³ / ₄	27 ³ / ₄	10	25	6 ¹ / ₂	-	Yes	
	7122	7142	7162	7182	Semi-Recessed	9	24	5 ³ / ₄	11 ³ / ₄	26 ³ / ₄	10	25	4	2	Yes	
	7123	7143	7163	7183	Semi-Recessed	9	24	5 ³ / ₄	11 ³ / ₄	26 ³ / ₄	10	25	3	3	Yes	
	7124	7144	7164	7184	Surface	11 ¹ / ₂	26 ¹ / ₂	6 ¹ / ₂	-	-	-	-	-	-	No	3020 3202 3320 3410
	7125	7145	7165	7185	Recessed	12	27	8	14 ³ / ₄	29 ³ / ₄	13	28	7 ³ / ₄	1/2	Yes	
	7126	7146	7166	7186	Trimless	12	27	8 ¹ / ₂	15 ³ / ₄	30 ³ / ₄	13	28	8 ³ / ₄	-	Yes	
	7127	7147	7167	7187	Semi-Recessed	12	27	8	14 ³ / ₄	29 ³ / ₄	13	28	5 ¹ / ₄	3	Yes	
	7128	7148	7168	7188	Semi-Recessed	12	27	8	14 ³ / ₄	29 ³ / ₄	13	28	3 ¹ / ₄	5	No	
	7129	7149	7169	7189	Surface	14 ⁵ / ₈	29 ³ / ₈	8	-	-	-	-	-	-	No	

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

Job Name: _____

Architect/Contractor: _____

Rep: _____

Page: _____ of _____

DATE:
June 2007

MODEL NUMBER
7107-7189 SERIES

FIRE RATED 7100 SERIES FIRE EXTINGUISHER CABINETS UL CLASSIFIED, 7N43

REGULARLY FURNISHED:

BOX- Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish.

DOOR AND FRAME



7107-7128 Series: Steel - Cold rolled steel with recoatable white polyester finish.

7130-7148 Series: Aluminum - Satin finish, clear polyester coated.


7150-7168 Series: Stainless Steel - #304 Stainless Steel with #4 finish.

7170-7188 Series: Brass - Polished finish, clear polyester coated.


Wall mounting and size of cabinet as selected by model number.



RECESSED



TRIMLESS



SEMI-RECESSED

Qty	Model No.				Wall Mounting	Inside Box Dimensions			Overall Frame		Minimum Wall Opening Required			Trim	ADA	For Use With These Extinguishers
	Steel	Aluminum	Stainless Steel	Brass		K	L	M	N	O	W	H	D			
	7107	7137	7157	7177	Recessed	9	18	5	11 3/4	20 3/4	11 1/4	20	5 5/8	1/2	Yes	3002
	7108	7138	7158	7178	Semi-Recessed	9	18	5	11 3/4	20 3/4	11 1/4	20	4 1/8	2	Yes	3005
	7110	7130	7150	7170	Recessed	9	24	5	11 3/4	26 3/4	11 1/4	26	5 5/8	1/2	Yes	3005-3
	7112	7132	7152	7172	Semi-Recessed	9	24	5	11 3/4	26 3/4	11 1/4	26	4 1/8	2	Yes	3302
	7113	7133	7153	7173	Semi-Recessed	9	24	5	11 3/4	26 3/4	11 1/4	26	3 1/8	3	Yes	3305
	7120	7140	7160	7180	Recessed	9	24	5 3/4	11 3/4	26 3/4	11 1/4	26	6 3/8	1/2	Yes	3305-3
	7121	7141	7161	7181	Trimless	9	24	6 1/4	12 3/4	27 3/4	11 1/4	26	7 3/8	-	Yes	3006
	7122	7142	7162	7182	Semi-Recessed	9	24	5 3/4	11 3/4	26 3/4	11 1/4	26	4 7/8	2	Yes	3010
	7123	7143	7163	7183	Semi-Recessed	9	24	5 3/4	11 3/4	26 3/4	11 1/4	26	3 7/8	3	Yes	3306
	7125	7145	7165	7185	Recessed	12	27	8	14 3/4	29 3/4	14 1/4	29	8 5/8	1/2	Yes	3310
	7126	7146	7166	7186	Trimless	12	27	8 1/2	15 3/4	30 3/4	14 1/4	29	9 5/8	-	Yes	3405
	7127	7147	7167	7187	Semi-Recessed	12	27	8	14 3/4	29 3/4	14 1/4	29	6 1/8	3	Yes	3020
	7128	7148	7168	7188	Semi-Recessed	12	27	8	14 3/4	29 3/4	14 1/4	29	4 1/8	5	No	3202

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

Job Name: _____

Architect/Contractor: _____

Rep: _____

Page: _____ of _____

DATE:
June 2007

MODEL NUMBER
FRC7107-FRC7188 SERIES