

# 7300 SERIES FIRE EXTINGUISHER CABINETS

## REGULARLY FURNISHED:

**BOX-** Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish, and a continuous hinge.

### DOOR AND FRAME

7307-7329 Series: Steel - Cold rolled steel with recoatable white polyester finish.


7337-7349 Series: Aluminum - Satin finish, clear polyester coated.

7357-7369 Series: Stainless Steel - #304 Stainless Steel with #4 finish.


7377-7389 Series: Brass - Polished finish, clear polyester coated.

Wall mounting and size of cabinet as selected by model number.


BUBBLE TYPE: CLEAR




**RECESSED**



**TRIMLESS**



**SEMI-RECESSED**



**SURFACE**

Qty	Model No.				Wall Mounting	Inside Box Dimensions			Overall Frame		Wall Opening Required			Proj.	Trim	ADA	For Use With These Extinguishers
	Steel	Aluminum	Stainless Steel	Brass		K	L	M	N	O	W	H	D				
	7307	7337	7357	7377	Recessed	9	18	4	11 3/4	20 3/4	10	19	3 3/4	2	1/2	Yes	3002, 3005, 3005-3, 3302, 3305, 3305-3
	7308	7338	7358	7378	Semi-Recessed	9	18	4	11 3/4	20 3/4	10	19	2 1/4	2	2	No	3005-3, 3302, 3305, 3305-3
	7309	7339	7359	7379	Surface	11 1/2	20 1/2	4	-	-	-	-	-	2	-	No	3002, 3005, 3005-3, 3006, 3010, 3302, 3305, 3305-3, 3306, 3310,
	7320	7340	7360	7380	Recessed	9	24	4	11 3/4	26 3/4	10	25	3 3/4	2	1/2	Yes	3002, 3005, 3005-3, 3006, 3010, 3302, 3305, 3305-3, 3306, 3310,
	7321	7341	7361	7381	Trimless	9	24	4 1/2	12 3/4	27 3/4	10	25	4 3/4	2	-	Yes	3002, 3005, 3005-3, 3006, 3010, 3302, 3305, 3305-3, 3306, 3310,
	7322	7342	7362	7382	Semi-Recessed	9	24	4	11 3/4	26 3/4	10	25	2 1/4	2	2	No	3002, 3005, 3005-3, 3006, 3010, 3302, 3305, 3305-3, 3306, 3310,
	7324	7344	7364	7384	Surface	11 1/2	26 1/2	4	-	-	-	-	-	2	-	No	3002, 3005, 3005-3, 3006, 3010, 3302, 3305, 3305-3, 3306, 3310,
	7325	7345	7365	7385	Recessed	12	27	4 3/4	14 1/2	29 1/2	13	28	4 1/2	3	1/2	Yes	3020, 3202, 3320, 3410
	7326	7346	7366	7386	Trimless	12	27	5 1/4	15 1/2	30 1/2	13	28	5 1/2	3	-	Yes	3020, 3202, 3320, 3410
	7327	7347	7367	7387	Semi-Recessed	12	27	4 3/4	14 1/2	29 1/2	13	28	3	3	3	No	3020, 3202, 3320, 3410
	7329	7349	7369	7389	Surface	14 1/2	29 1/2	4 3/4	-	-	-	-	-	3	-	No	3020, 3202, 3320, 3410

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

Job Name: \_\_\_\_\_  
 Architect/Contractor: \_\_\_\_\_  
 Rep: \_\_\_\_\_  
 Page: \_\_\_\_\_ of \_\_\_\_\_

DATE:  
 Rev. Mar. 22, 2009

**MODEL NUMBER**  
**7307-7389 SERIES**



# FIRE RATED 7300 SERIES FIRE EXTINGUISHER CABINETS UL CLASSIFIED, 7N43

## REGULARLY FURNISHED:

**BOX-** Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish, and a continuous hinge.

### DOOR AND FRAME



7307-7327 Series: Steel - Cold rolled steel with recoatable white polyester finish.

7337-7347 Series: Aluminum - Satin finish, clear polyester coated.


7357-7367 Series: Stainless Steel - #304 Stainless Steel with #4 finish.

7377-7387 Series: Brass - Polished finish, clear polyester coated.


Wall mounting and size of cabinet as selected by model number.



**RECESSED**



**TRIMLESS**



**SEMI-RECESSED**

Qty	Model No.				Wall Mounting	Inside Box Dimensions			Overall Frame		Wall Opening Required			Proj.	Trim	ADA	For Use With These Extinguishers
	Steel	Aluminum	Stainless Steel	Brass		K	L	M	N	O	W	H	D				
	7307	7337	7357	7377	Recessed	9	18	4	11 <sup>3</sup> / <sub>4</sub>	20 <sup>3</sup> / <sub>4</sub>	11 <sup>1</sup> / <sub>4</sub>	20	4 <sup>5</sup> / <sub>8</sub>	2	1 <sup>1</sup> / <sub>2</sub>	Yes	3002, 3005, 3005-3 3302, 3305, 3305-3
	7308	7338	7358	7378	Semi-Recessed	9	18	4	11 <sup>3</sup> / <sub>4</sub>	20 <sup>3</sup> / <sub>4</sub>	11 <sup>1</sup> / <sub>4</sub>	20	3 <sup>1</sup> / <sub>8</sub>	2	2	No	3302, 3305, 3305-3
	7320	7340	7360	7380	Recessed	9	24	4	11 <sup>3</sup> / <sub>4</sub>	26 <sup>3</sup> / <sub>4</sub>	11 <sup>1</sup> / <sub>4</sub>	26	4 <sup>5</sup> / <sub>8</sub>	2	1 <sup>1</sup> / <sub>2</sub>	Yes	3002, 3005, 3005-3 3006, 3010, 3302, 3305, 3305-3, 3306
	7321	7341	7361	7381	Trimless	9	24	4 <sup>1</sup> / <sub>2</sub>	11 <sup>3</sup> / <sub>4</sub>	26 <sup>3</sup> / <sub>4</sub>	11 <sup>1</sup> / <sub>4</sub>	26	5 <sup>5</sup> / <sub>8</sub>	2	-	Yes	3305, 3305-3, 3306
	7322	7342	7362	7382	Semi-Recessed	9	24	4	11 <sup>3</sup> / <sub>4</sub>	26 <sup>3</sup> / <sub>4</sub>	11 <sup>1</sup> / <sub>4</sub>	26	3 <sup>1</sup> / <sub>8</sub>	2	2	No	3310
	7325	7345	7365	7385	Recessed	12	27	4 <sup>3</sup> / <sub>4</sub>	14 <sup>1</sup> / <sub>2</sub>	26 <sup>3</sup> / <sub>4</sub>	14 <sup>1</sup> / <sub>4</sub>	29	5 <sup>3</sup> / <sub>8</sub>	3	1 <sup>1</sup> / <sub>2</sub>	Yes	3020
	7326	7346	7366	7386	Trimless	12	27	5 <sup>1</sup> / <sub>4</sub>	14 <sup>1</sup> / <sub>2</sub>	26 <sup>3</sup> / <sub>4</sub>	14 <sup>1</sup> / <sub>4</sub>	29	6 <sup>3</sup> / <sub>8</sub>	3	-	Yes	3202
	7327	7347	7367	7387	Semi-Recessed	12	27	4 <sup>3</sup> / <sub>4</sub>	14 <sup>1</sup> / <sub>2</sub>	26 <sup>3</sup> / <sub>4</sub>	14 <sup>1</sup> / <sub>4</sub>	29	2 <sup>7</sup> / <sub>8</sub>	3	3	No	3320 3410

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

Job Name: \_\_\_\_\_

Architect/Contractor: \_\_\_\_\_

Rep: \_\_\_\_\_

Page: \_\_\_\_ of \_\_\_\_

DATE:  
Rev. Mar. 22, 2009

**MODEL NUMBER**  
FRC7307-FRC7388 SERIES