

# 8000 SERIES VALVE CABINETS

## REGULARLY FURNISHED:

**BOX-** Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish, and a continuous hinge.

### DOOR AND FRAME


8020-8029 Series: Steel - Cold rolled steel with recoatable white polyester finish.

8040-8049 Series: Aluminum - Satin finish, clear polyester coated.


8060-8069 Series: Stainless Steel - #304 Stainless Steel with #4 finish.

8080-8089 Series: Brass - Polished finish, clear polyester coated.


Wall mounting and size of cabinet as selected by model number.




**RECESSED**



**TRIMLESS**



**SEMI-RECESSED**



**SURFACE**

Qty	Model No.				Wall Mounting	Inside Box Dimensions			Overall Frame		Wall Opening Required			Trim	Inlet Location			Shelf	ADA	For Use With	
	Steel	Aluminum	Stainless Steel	Brass		K	L	M	N	O	W	H	D		X	Y	Z				Z-Z
	8020	8040	8060	8080	Recessed	18	18	8	21 <sup>3/4</sup>	21 <sup>3/4</sup>	19	19	8 <sup>1/2</sup>	-	4	4	9	-	Yes	2 <sup>1/2</sup> " Angle Valve	
	8021	8041	8061	8081	Trimless	18	18	8 <sup>3/4</sup>	21	21	19	19	9 <sup>1/4</sup>	-	4	4	9	-	Yes		
	8022	8042	8062	8082	Semi-Recessed	18	18	8	21 <sup>1/2</sup>	21 <sup>1/2</sup>	19	19	6 <sup>1/2</sup>	2	4	4	9	-	Yes		
	8024	8044	8064	8084	Surface	20	20	9 <sup>1/4</sup>	-	-	-	-	-	-	-	-	-	-	-	No	Up to 20lb. Dry Chem Fire Ext. & 2 <sup>1/2</sup> " Angle Valve
	8025	8045	8065	8085	Recessed	14	40	8	17 <sup>3/4</sup>	43 <sup>3/4</sup>	15	41	8 <sup>1/2</sup>	-	4	4	9	12	Yes		
	8026	8046	8066	8086	Trimless	14	40	8 <sup>3/4</sup>	17	43	15	41	9 <sup>1/4</sup>	-	4	4	9	12	Yes		
	8027	8047	8067	8087	Semi-Recessed	14	40	8	17 <sup>1/2</sup>	43 <sup>1/2</sup>	15	41	6 <sup>1/2</sup>	3	4	4	9	12	Yes		
	8029	8049	8069	8089	Surface	16	42	9 <sup>1/4</sup>	-	-	-	-	-	-	-	-	-	12	No		

ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

Job Name: \_\_\_\_\_

Architect/Contractor: \_\_\_\_\_

Rep: \_\_\_\_\_

Page: \_\_\_\_\_ of \_\_\_\_\_

DATE:  
January 2009

**MODEL NUMBER**  
**8020-8089 SERIES**

# FIRE RATED 8000 SERIES VALVE CABINETS UL CLASSIFIED, 7N43

## REGULARLY FURNISHED:

**BOX-** Cold rolled steel with an electrostatically applied, thermally-fused polyester coating with recoatable white finish, and a continuous hinge.

### DOOR AND FRAME

8020-8027 Series: Steel - Cold rolled steel with recoatable white polyester finish.

8040-8047 Series: Aluminum - Satin finish, clear polyester coated.


8060-8067 Series: Stainless Steel - #304 Stainless Steel with #4 finish.

8080-8087 Series: Brass - Polished finish, clear polyester coated.


Wall mounting and size of cabinet as selected by model number.

Qty	Model No.				Wall Mounting	Inside Box Dimensions			Overall Frame		Wall Opening Required			Trim	Shelf	ADA	For Use With
	Steel	Aluminum	Stainless Steel	Brass		K	L	M	N	O	W I D T H	H E I G H T	D E P T H				
	8020	8040	8060	8080	Recessed	18	18	8	21 <sup>3</sup> / <sub>4</sub>	21 <sup>3</sup> / <sub>4</sub>	20 <sup>1</sup> / <sub>4</sub>	20	9 <sup>3</sup> / <sub>4</sub>	-	-	Yes	2 1/2" Angle Valve
	8021	8041	8061	8081	Trimless	18	18	8 <sup>3</sup> / <sub>4</sub>	21	21	20 <sup>1</sup> / <sub>4</sub>	20	10 <sup>1</sup> / <sub>2</sub>	-	-	Yes	
	8022	8042	8062	8082	Semi-Recessed	18	18	8	21 <sup>1</sup> / <sub>2</sub>	21 <sup>1</sup> / <sub>2</sub>	20 <sup>1</sup> / <sub>4</sub>	20	7 <sup>3</sup> / <sub>4</sub>	2	-	Yes	
	8025	8045	8065	8085	Recessed	14	40	8	17 <sup>3</sup> / <sub>4</sub>	43 <sup>3</sup> / <sub>4</sub>	16 <sup>1</sup> / <sub>4</sub>	42	9 <sup>3</sup> / <sub>4</sub>	-	12	Yes	Up to 20lb. Dry Chem Fire Ext. & 2 1/2" Angle Valve
	8026	8046	8066	8086	Trimless	14	40	8 <sup>3</sup> / <sub>4</sub>	17	43	16 <sup>1</sup> / <sub>4</sub>	42	10 <sup>1</sup> / <sub>2</sub>	-	12	Yes	
	8027	8047	8067	8087	Semi-Recessed	14	40	8	17 <sup>1</sup> / <sub>2</sub>	43 <sup>1</sup> / <sub>2</sub>	16 <sup>1</sup> / <sub>4</sub>	42	7 <sup>3</sup> / <sub>4</sub>	3	12	Yes	


ALL DIMENSIONS ARE IN INCHES UNLESS NOTED OTHERWISE



**RECESSED**



**TRIMLESS**



**SEMI-RECESSED**

Job Name: \_\_\_\_\_

Architect/Contractor: \_\_\_\_\_

Rep: \_\_\_\_\_

Page: \_\_\_\_\_ of \_\_\_\_\_

DATE:

January 2009

**MODEL NUMBER**

**FRC8020-FRC8087 SERIES**