




Lighting



Hand hygiene



Personal care



Air quality



Our business and leisure environments are under closer scrutiny than ever before. From the air we breathe, to the level of light, or the hygiene in washrooms, it all affects the experiences of customers and employees.

Technology can help or hinder these experiences. When it doesn't work properly, it can have a negative effect on our performance, our happiness and even our well-being. Technology that does work properly, on the other hand, can improve our lives.



dyson **cu beam duo**

Combined up and down light
with full flexible control.

Powerful up and down light from one product.

Custom-engineered lens and trim blades
project direct light precisely where you need it.



The down-light projects up to 722lx at 4000K evenly
over an area of 10.5ft x 5.3ft / 3.2m x 1.6m when
mounted 4.3ft / 1.3m above the task area.¹

The up-light projects up to 733lx at 4000K
evenly over an area of 4m wide when mounted
at a 15.8in / 400mm drop height from the ceiling.¹

High efficacy with up to 113 lm/W at 4000K.

Weighs only 7lb / 3.2kg.

5 year warranty (parts only).



¹Based on 50/50 split of up and down light.

The up-light casts a wide pool of indirect light on the ceiling for illuminating open spaces, and the down-light creates focused, adjustable task lighting for working.



dyson **cu beam down**

Suspended down-light with a controlled pool of powerful illumination.

Powerful LED light (5350lm at 4000K).

Custom-engineered lens and trim blades project direct light precisely where you need it.



LEDs stay bright for up to 180,000 hours.²

Projects up to 674lx at 4000K evenly over an area of 10.5ft x 5.3ft / 3.2m x 1.6m when mounted 4.3ft / 1.3m above the task area.

High efficacy with up to 94 lm/W at 4000K.

Weighs only 6lb 6oz / 2.9kg.

5 year warranty (parts only).



²Calculated lifetime based on LED L70.

Perfect for task surfaces such as meeting tables, reception desks, offices and dining areas.



dyson **cu beam up**

Suspended up-light with an ultra-wide distribution of powerful illumination.

Powerful LED light (7800lm at 4000K).

Custom engineered lens projects wide beam of ambient light precisely where you need it.


Stays brights for up to 180,000 hours.²

Projects up to 690lx at 4000K evenly over an area of 13ft / 4m wide when mounted at 15.8in / 400 mm drop height from the ceiling.

High efficacy with up to 92 lm/W at 4000K.

Weighs only 6lb 6oz / 2.9kg.

5 year warranty (parts only).



Silver



Black



White

²Calculated lifetime based on LED L70.

Makes indirect lighting possible, creating ambient lighting for open environments like atriums, foyers, circulation areas and general office space.



dyson csys

**Powerful warm white task light.
Engineered for use in a relaxing space.**

Powerful LED light (648lx). Measured from
1.9ft / 0.6m distance over 10.7ft² / 1m² task area.

Stays precisely where you need it.

Touch sensitive continuous dimming.

Conical reflectors help to reduce glare.

LEDs stay bright for up to 144,000 hours*
due to Heat pipe technology.

Uses a fraction of the energy of some
conventional halogen desk lights.

2 year warranty (parts only).

Colorways – Floor and Clamp: Black/Silver, Black/Black.
Desk: Black/Silver, Black/Black or White/Silver.



*Calculated lifetime based on LED L70.

CSYS™ task lights give hotel guests powerful warm white light. They can position it precisely where it's needed, to suit working and reading.



dyson csys 4k

Powerful cool white task light.
Engineered for the office environment.

Powerful LED light (808lx). Measured from 1.9ft / 0.6m distance over 10.7ft² / 1m² task area.

High-efficiency LEDs provide 30% more lumens per watt than our original model.

Stays precisely where you need it.

Touch sensitive continuous dimming.

Conical reflectors help to reduce glare.

LEDs stay bright for up to 144,000 hours² due to Heat pipe technology.

Uses a fraction of the energy of some conventional halogen desk lights.

2 year warranty (parts only).

Colorways – Clamp: Black/Silver, Black/Black.
Desk: Black/Silver, Black/Black or White/Silver.



²Calculated lifetime based on LED L70.

Cool white light can create an office-like environment. CSYS™ 4K task lights provide 25% more light on the task plane than the original CSYS™ task light (2700K).



dyson airblade dB

The fastest, most
hygienic hand dryer.³

12 second dry time.⁴

HEPA filter captures 99.97% of particles
the size of bacteria as small as 0.3 microns.

Tested and certified by NSF International.

Certified for use in food environments
by HACCP International.

Costs just \$40 to run per year.⁵

Small carbon footprint.

Tough and durable.

Touch-free operation.

Contains antimicrobial additive.

5 year warranty – parts and labor.



HACCP International non-food certification mark is the registered trademark of HACCP International. HACCP International have certified Dyson products based on their recommended installation and operating conditions. The NSF logo is the registered trademark of NSF International.

³Based on overall dry time performance and HEPA filtration capabilities. ⁴Dry time measured using Dyson test method 769 based on NSF P335 using a measurement of 0.1g residual moisture. ⁵For calculations visit dyson.com/calcs



Gray



White

Engineered for high footfall locations where fast hand drying is paramount. Also approved for food preparation environments.



dyson airblade V

The most hygienic hand dryer is 30% quieter.⁶

Certified by Quiet Mark.

HEPA filters capture 99.97% of particles the size of bacteria as small as 0.3 microns.

Tested and certified by NSF International.

12 second dry time.⁴

Costs just \$31 to run per year.⁵

Small carbon footprint.

Slim profile – just 4 inches deep, no recessing required.

Touch-free operation.

Contains antimicrobial additive.

5 year warranty – parts and labor.



Quiet Mark is a registered trademark of the Noise Abatement Society.
The NSF logo is the registered trademark of NSF International.

⁴Dry time measured using Dyson test method 769 based on NSF P335 using a measurement of 0.1g residual moisture.

⁵For calculations visit [dyson.com/calcs](https://www.dyson.com/calcs) ⁶Loudness reduction compared to the original Dyson Airblade V hand dryer.

Sprayed nickel



White



Engineered for noise sensitive environments and washrooms where saving space is important.



dyson airblade tap

Airblade™ hand drying technology in a tap.

Wash and dry hands at the sink.

No water dripped on the floor.

14 second dry time.⁴

HEPA filter captures 99.97% of particles the size of bacteria as small as 0.3 microns.

Tested and certified by NSF International.

Certified for use in food environments by HACCP International.

Costs just \$48 to run per year.⁵

Small carbon footprint.

Saves space.

5 year warranty – parts and labor.



HACCP International non-food certification mark is the registered trademark of HACCP International. HACCP International have certified Dyson products based on their recommended installation and operating conditions. The NSF logo is the registered trademark of NSF International.

⁴Dry time measured using Dyson test method 769 based on NSF P335 using a measurement of 0.1g residual moisture. ⁵For calculations visit dyson.com/calcs

Designed for washrooms where space limitation and wet floors are a problem. Also approved for food preparation environments.



dyson supersonic

**Intelligent heat control for shine.
Powerful digital motor.**

Thermistor guards against extreme heat damage to protect natural shine.

Fast drying.

Engineered for balance.

Smooth and controlled drying.

Acoustically tuned.

Negative ions.

Magnetic attachments.

Cool to touch.

No grill. No caught hair.

2 year warranty – parts and labor.



Iron/Fuchsia



White/Silver

Creates a styling experience rather than just functional drying. Three magnetic attachments allow the user to dry and style at the same time.



dyson pure coollink

Automatically removes 99.97% of allergens and pollutants as small as 0.3 microns from the air. Purifying fan in warmer weather.

Captures fumes and odors.

Purifies all year round.

Purifying fan in warmer weather.

Automatically monitors, reacts and purifies – then reports to your Dyson Link app.⁶ So you can remotely control your environment.

Night-time automode for lighter sleepers.

2 year warranty – parts and labor.



Certified asthma & allergy friendly™ by Allergy Standards Limited.

The CERTIFIED ASTHMA & ALLERGY FRIENDLY mark is a registered certification mark of the ASTHMA AND ALLERGY FOUNDATION OF AMERICA and ALLERGY STANDARDS LTD.

Quiet Mark is a registered trademark of the Noise Abatement Society.

⁶Standard data and messaging rates apply. Requires Wifi and app-enabled device.

Engineered to create cleaner air
with powerful purified airflow
for personal cooling.



dyson pure hot+cool link

**Intelligently purifies, heats and cools you.
Automatically removes 99.97% of
allergens and pollutants as small
as 0.3 microns from the air.**

Purifies all year round. Heats with
thermostat control in colder weather.
Cooling fan in warmer weather.

Captures odors and potentially
harmful VOC's like paint fumes.

Concentrated airflow for personal
use or diffused mode.

Automatically monitors, reacts and purifies –
then reports to your Dyson Link app.⁶ So you
can remotely control your environment.

Night-time automode for lighter sleepers.

2 year warranty – parts and labor.



Certified asthma & allergy friendly™ by Allergy Standards Limited.
The CERTIFIED ASTHMA & ALLERGY FRIENDLY mark is a registered
certification mark of the ASTHMA AND ALLERGY FOUNDATION
OF AMERICA and ALLERGY STANDARDS LTD.
Quiet Mark is a registered trademark of the Noise Abatement Society.



⁶Standard data and messaging rates apply. Requires Wifi and app-enabled device.

Engineered to create cleaner air
with powerful purified airflow for
personal heating and cooling.



“For technology to have a positive effect, it must work properly. By solving problems and relentlessly innovating, we strive to set new standards for performance and well-being in business and leisure environments.”

James Dyson



For further information contact:

888-397-6622

www.dyson.com

dyson