

# MAX-ACCESS PLATFORMS




## Maximum flexibility for maximum access options!

## Design your own platform to suit any application where work is being done at height.

The Max-Access Platforms allow you to design your own complete platform and ladder configuration to suit any application where work is being done at height. The platform components can be used together for more width or length. You can create a custom multi-tiered system by using the various ladder and stair components available. The versatility of the platforms' ability of being connected to any other component truly gives you the maximum access options!


### Example Configuration

- Platform components can be used together for more width or length
- Stairs or Ladders can connect different levels to create multi-tiered systems
- Foot plates have holes for anchoring down



### Features:

- Lightweight aluminum construction
- Gray and yellow powder-coated finish
- Serrated grating platform surface and stair treads
- Perforated non-slip ladder rungs
- 750 lb. rated capacity



# MAX-ACCESS PLATFORMS



## STAIR UNIT - 50° INCLINE

SERRATED							
# of Steps	Tri-Arc Model #	Step Width	Step Depth	Platform Height	Overall Height	Overall Width	Overall Depth
2	UAP0250	26"	9.5"	20"	59.5"	34"	18.5"
3	UAP0350	26"	9.5"	30"	69.5"	34"	27.0"
4	UAP0450	26"	9.5"	40"	79.5"	34"	35.5"
5	UAP0550	26"	9.5"	50"	89.5"	34"	44.0"
6	UAP0650	26"	9.5"	60"	99.5"	34"	52.0"
7	UAP0750	26"	9.5"	70"	109.5"	34"	60.5"
8	UAP0850	26"	9.5"	80"	119.5"	34"	69.0"
9	UAP0950	26"	9.5"	90"	129.5"	34"	77.5"
10	UAP1050	26"	9.5"	100"	139.5"	34"	85.5"
11	UAP1150	26"	9.5"	110"	149.5"	34"	94.0"

## TOWER SUPPORT

Tri-Arc Model #	For Platform Height of
UAP020	20"
UAP030	30"
UAP040	40"
UAP050	50"
UAP060	60"
UAP070	70"
UAP080	80"
UAP090	90"
UAP100	100"
UAP110	110"

Tower Supports required with:

- Every 50° and 90° ladder
- When 3 Platform Units are combined (every 108")




## LADDER UNIT - 90° INCLINE

PERFORATED							
# of Steps	Tri-Arc Model #	Step Width	Step Depth	Platform Height	Overall Height	Overall Width	Overall Depth
2	UAP0290	24"	1.625"	20"	62"	30"	9"
3	UAP0390	24"	1.625"	30"	72"	30"	9"
4	UAP0490	24"	1.625"	40"	82"	30"	9"
5	UAP0590	24"	1.625"	50"	92"	30"	9"
6	UAP0690	24"	1.625"	60"	102"	30"	9"
7	UAP0790	24"	1.625"	70"	112"	30"	9"
8	UAP0890	24"	1.625"	80"	122"	30"	9"
9	UAP0990	24"	1.625"	90"	132"	30"	9"
10	UAP1090	24"	1.625"	100"	142"	30"	9"
11	UAP1190	24"	1.625"	110"	152"	30"	9"



## PLATFORM UNIT

SERRATED			
Tri-Arc Model #	Length	Width	Thickness
UAP3636	36"	36"	5"



## HANDRAIL

Tri-Arc Model #	Top Rail Height
UAPHR1	42"

