

OFFICE LADDERS

Built with 100% square tube framework for a clean look, Office Ladders come in four standard colors to match your office decor. 300 lbs capacity. Rigid 1" square tubing. Spring loaded 3" casters provide mobility while rubber tipped legs add traction while in use. 16" and 24" wide steps available. Steps are 7" deep with deeper 14" top step. Solid treads covered with nonslip adhesive runner. Meets OSHA standards.



Item B1893231



Item B2144624



EGA PRODUCTS
MANUFACTURERS OF MATERIAL HANDLING AND STORAGE EQUIPMENT

Model	B2144625	B2144624	B1893231	B1893196	B2144626	B2124098
# of Steps	2	3	3	3	4	5
Platform Height	20"	30"	30"	30"	40"	50"
Platform Width	17"	17"	17"	17"	17"	17"
Platform Depth	14"	14"	14"	14"	14"	14"
O/A Height	44"	30"	54"	54"	64"	80"
O/A Width	22"	22"	22"	22"	22"	23"
O/A Length	23"	27"	27"	27"	36"	50"
Assembled	Assembled	Assembled	Assembled	Assembled	Assembled	Assembled
Brand	EGA Products	EGA Products	EGA Products	EGA Products	EGA Products	EGA Products
Capacity	450 lbs	450 lbs	450 lbs	450 lbs	450 lbs	450 lbs
Color Finish	Gray	Almond	Almond	Gray	Black	Almond
Construction	Steel	Steel	Steel	Steel	Steel	Steel
Incline Angle	60°	60°	60°	60°	60°	60°