

Box Dumpers

Valley Craft's versatile Box Dumpers are designed to manage the heaviest of loads. All dumpers bolt directly to the floor, ensuring reliability and stability throughout operation. Product features include:

- Load Capacity: models range from 2,000 - 6,000 pounds
- Dump Height: models available in 36", 48", 60", and 72"*
- Operation: Hydraulic up / Gravity down system
- Rotary switch control activates chute
- Adjustable hold down bar accommodates various container heights of 30" - 42" (on 2-inch centers)
- Heavy duty, all-welded steel construction with durable powder coat finish in green
- Includes corded hand control box with magnetic back



F80178A8
60" Box Dumper

*72" dump height models in 4000-lb and 6000-lb capacities have chute elevated 12" off the floor. Fork lift required for loading.

2,000 LB Capacity

Model No.	Dump Height	Chute L x W	Chute Reach	Frame Width	Horizontal Clearance	Overhead Clearance	Weight (lbs)
F80193A3	36"	36 x 36"	12½"	51"	72"	111"	1,226
F80184A4	36"	48 x 51"	12½"	66"	81"	119"	1,525
F80190A0	48"	36 x 36"	10"	51"	79"	127"	1,400
F80181A1	48"	48 x 51"	10"	66"	87"	135"	1,575
F80187A7	60"	36 x 36"	5"	51"	83"	138"	1,400
F80178A8	60"	48 x 51"	5"	66"	91"	146"	1,668
F80175A5	72"	36 x 36"	5"	51"	92"	159"	1,675
F80172A2	72"	48 x 51"	5"	66"	98"	167"	1,950

4,000 LB Capacity

Model No.	Dump Height	Chute L x W	Chute Reach	Frame Width	Horizontal Clearance	Overhead Clearance	Weight (lbs)
F80192A2	36"	36 x 36"	12½"	51"	72"	111"	1,500
F80183A3	36"	48 x 51"	12½"	66"	81"	119"	1,800
F80189A9	48"	36 x 36"	10"	51"	79"	127"	1,600
F80180A0	48"	48 x 51"	10"	66"	87"	135"	2,100
F80186A6	60"	36 x 36"	5"	51"	83"	138"	1,750
F80177A7	60"	48 x 51"	5"	66"	91"	146"	2,000
F80174A4*	72"	36 x 36"	5"	51"	83"	149"	2,000
F80171A1*	72"	48 x 51"	5"	66"	91"	158"	2,275

6,000 LB Capacity

Model No.	Dump Height	Chute L x W	Chute Reach	Frame Width	Horizontal Clearance	Overhead Clearance	Weight (lbs)
F80191A1	36"	36 x 36"	12½"	51"	72"	111"	1,500
F80182A2	36"	48 x 51"	12½"	66"	81"	119"	1,825
F80188A8	48"	36 x 36"	10"	51"	79"	127"	1,600
F80179A9	48"	48 x 51"	10"	66"	87"	135"	2,100
F80185A5	60"	36 x 36"	5"	51"	83"	138"	1,750
F80176A6	60"	48 x 51"	5"	66"	91"	146"	2,000
F80173A3*	72"	36 x 36"	5"	51"	83"	149"	2,000
F80170A0*	72"	48 x 51"	5"	66"	91"	158"	2,275