

Catalog Number
Notes
Type

FEATURES & SPECIFICATIONS

INTENDED USE — Provides a minimum of 90 minutes illumination for the rated wattage upon loss of AC power to meet code required emergency lighting. Ideal for applications requiring low profile, exit and emergency combo for lower mounting heights.

CONSTRUCTION — The housing is a standard white thermoplastic with a compact and low-profile design with all-inclusive lamp, reflector and lens assembly. It is 5VA flame rated and impact-resistant.

OPTICS — The typical life of the LED is 10 years. One, 0.75W white LED per lamp head.

ELECTRICAL — Dual-voltage 120/277 standard. Optional dual-voltage 120/230 50/60Hz available.

Bi-color LED status indicator for battery condition. (Green-normal, Red-check battery).

Two watts of remote capacity available.

BATTERY: 3.6V Maintenance-free, rechargeable, nickel-cadmium.

INSTALLATION — Top, side and back mount. Mounting pattern on canopy (top and side mount) and back plate (back mount) fits most standard size junction boxes.

LISTINGS — UL Listed. Meets all applicable requirements for UL 924, NFPA 101 (current Life Safety Code), NFPA 70 (NEC), FCC and OSHA. Indoor damp location 50° to 104°F (10°C to 40°C) listed.

WARRANTY — 2-year limited warranty. Complete warranty terms located at:

www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

NOTE: Actual performance may differ as a result of end-user environment and application.

All values are design or typical values, measured under laboratory conditions at 25 °C.

Specifications subject to change without notice.


Low Profile Emergency Light/Exit Combo

ECC



MOUNTING AND SPECIFICATIONS

All dimensions are inches (centimeters) unless otherwise indicated.



Specifications

- Length: 16 (40.64)
- Depth: 1.94 (4.93)
- Height: 7.25 (18.42)
- Weight: 2.15lbs (.98kg)

ECC Low Profile Emergency Light/Exit Combo

ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: ECC R

Series	Housing Color	Letter color	Options
ECC	(Blank) White	R Red G Green	(Blank) Not Required REM Remote Capacity

BATTERY CAPACITY AND LOADING

Battery	Total Capacity	Maximum# Remote Lamp Heads*
3.6V	3.5W	2 - ERE SGL M24
		1 - ERE T M24
		2 - ERE GY SGL WP M12
		1 - ERE GY T WP M12

*These are in addition to the lamp heads on the product.

ELECTRICAL SPECIFICATIONS

Description	Supply Voltage	Input Wattage		Input Amps	
		120	277	120	277
Standard (No options)	120/277	1.1	1.3	.08	.09
Remote Capacity Option (REM)	120/277	1.6	1.6	.12	.11

Accessories: Order as separate catalog number.

ERE SGL	Single, indoor remote head, white, 0.5W, 3.6V. See specsheet ERE .
ERE T	Twin, indoor remote head, white, 1W. See specsheet ERE .
ERE GY SGL WP	Single, weather-proof remote head, gray, 1W, 3.6V, 6V, 9.6V & 12V. See specsheet ERE .
ELA WG3	Wireguard, 30" W x 13-1/2" H x 6" D. See specsheet ELA-WG .
ELA WG2M	Wireguard, 21-1/4" W x 15" H x 12" D. See specsheet ELA-WG .