

LED **Versi** Lite™

Flush Mounts **Redefined**



Our most versatile LED Flush Mount for any space.

Available in a variety of sizes and finishes, the LED Versi Lite offers an energy-efficient lighting solution for an array of residential and light commercial spaces, both indoor and outdoor.

- Hallways
- Corridors
- Porches
- Closets
- Pantries
- Utility Rooms
- Small Rooms
- Bathrooms
- Showers
- Stairways
- Work Areas
- *And much more!*




Lithonia Lighting has updated their most advanced LED flush mount to date — the **LED Versi Lite™**. **Designed for simplicity, the fixture includes the sophisticated microDRIVE™ Technology which eliminates the need for an LED driver.** The LED Versi Lite delivers **increased efficacy** and reliability all while **reducing Total Harmonic Distortion (THD)** and maximizing power factor. **Our most versatile LED Flush Mount for any space.**



Able to mount to ceiling or wall

- Comparable light output to a 60W (7") or 2-75W (13") incandescent with an **84% reduction in power consumption**
- 50,000 hour L70 Rated Life
- Dimmable to 10% on most standard triac dimmers
- **Low THD** of less than 20
- High Power Factor of greater than 0.98
- 3 color temperatures to choose from - 2700K, 3000K and 4000K
- Wet location option



Annual Energy + Replacement Savings = Total Annual Savings

¹Cost based on 8hrs. of operation at 0.13 KWH.

ORDERING INFORMATION

For shortest lead times, configure products using **bold options**.

Example: **FMML 7 840 DDBT WL**

FMML Versi Lite LED

Series	Size	CRI	Color Temperature (7"/13")	Fixture Finish	Options
FMML LED Versi Lite Flushmount	7 7" Diameter 13 13" Diameter	8 >80	40 4000K (660lm/1985lm) 30 3000K (642lm/1900lm) 27 2700K (612lm/1770lm)	(blank) Textured White DDBT Textured Bronze DNA Natural Aluminum	WL Wet Location

