

CSO71AE Honeywell Evaporative Air Cooler

Cools up to 100 square feet*

Product Features:

- Natural, energy-efficient cooling with no compressor
- Honeycomb Cooling Media - Highly efficient for fast cooling performance
- Unpack, add water, plug it in, and use
- Cools up to 100 square feet*
- Power consumption of 50 watts
- Full-function remote control
- User-friendly LED display
- Oscillating louvers
- Durable casters for easy mobility
- 0.5 to 7.5 hours auto shut-off timer

Product Description:



Classy design, compact structure, lightweight & super-low power consumption make this an ideal companion during hot & dry seasons.

The Honeywell CSO71AE Evaporative Air Cooler is ideal for spot cooling in any home or office. Three fan speeds and oscillating louvers improve air circulation and provide an even distribution of cool air. Optimum cooling is provided by the Honeycomb Cooling Media and the carbon dust filter cleanses the air. The unit consumes only 50 watts of power and includes an automatic shutoff timer for even more energy saving. The electronic control panel is easy to use and the all functions can be operated with the remote control. This 12.3 lbs. lightweight unit has 4 durable casters for easy mobility from room to room.

Natural, energy-efficient cooling with no compressor: The CSO71AE is built to maximize energy efficiency and keep costs low. Warm air is drawn into the cooler through a dust and odor-reducing carbon filter and enters the Honeycomb Cooling Media. Water pumped from the tank pours over the media and as the warm air passes through, the water absorbs the heat, naturally cooling and

humidifying the air. A fan propels the cooled air out into the room. This no-compressor system cools naturally, efficiently and inexpensively.

WHAT'S THE SECRET TO HIGHLY EFFICIENT, NATURAL HEAT ABSORPTION? The CSO71AE is equipped with Honeycomb Cooling Media made of special cellulose paper and specially designed angles which allow air to travel through at high speed with little resistance and more surface area to absorb heat from the air. Honeycomb media cools more efficiently than other types of media for the same amount of energy.

Not an Air Conditioner (Important - Please Read!)

The Evaporative Air Cooler is not an air conditioner as it does not use a compressor or refrigerant gas. It should not be expected to cool to the same degree as a refrigerated air conditioner. It works best in hot and dry conditions.

Please refer to the User Manual and Warranty for additional information.

This product has a 1 year limited warranty.

ADDITIONAL FEATURES:

- 0.5 to 7.5 hour Automatic Shut-off Timer
- 1.8 gallons Water Tank Capacity.

What's In the Box?

- 1 Honeywell CSO71AE Evaporative Air Cooler
- Instruction Manual
- Remote control

*under test conditions

Specifications and Dimensions	CS071AE
Recommended Square Footage	100 Sq. Ft.
Residential/Industrial	Residential
Indoor/Outdoor	Indoor
Type	Portable
Product Height	25.4 in.
Product Width	15 in.
Product Depth	9.8 in.
Package Weight	15.4 lbs.
Number of Fan Speeds	3
Amount of Air Moved (Max CFM)	150 CFM
Air Movement	Blower
Oscillating Louvers	Yes
Water Reservoir Capacity	1.8 gallons
Water Level Indicator	Yes
Hose Hookup	No
Controls	Electronic
Remote Control	Yes
Programmable Timer	Yes
Casters	Yes
Color	White
Voltage	120 V
Watts	50 W
Amperage	0.45 Amps