

CT66JBIFR



33.25" x 23.63" x 23.5" (H x W x D)

Built-in undercounter refrigerator-freezer for general purpose use, with dual evaporator cooling, SS door frame for panel inserts, and white cabinet

Highlights:

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel door frame accepts slide-in panels for a custom look

Improved temperature performance with our unique dual evaporator cooling

Zero degree freezer compartment

Product Features:

Slim undercounter dimensions	Ideal 24" footprint offers full 5.1 cu.ft. storage capacity in a slim fit
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinetry
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel door frame	Slide a panel into this two-piece exposed stainless steel door frame to match the unit to other cabinetry (panel size: 23" W x 28" H at up to 1/4" thick)
Pro style handle	Stainless steel handle adds an attractive touch
Reversible door	User-reversible door swing for added flexibility
Dual evaporator cooling	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Zero degree freezer	Static manual defrost freezer section offers more stability

CT66JBIFR Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	34.75"
Width	23.63"
Depth	23.5"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Panel-Ready
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	104.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	3
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Fan Type	Exterior
Freon	R134a
Freon Amount	2.6

High Side PSI	285.0
Low Side PSI	70.0
Level Legs	4
Compressor Step Height	7.0"
Compressor Step Width	20.5"
Compressor Step Depth	5.0"

