

CT66JBISSHVADA



32" x 23.63" x 23.5" (H x W x D)

Built-in undercounter ADA compliant refrigerator-freezer for general purpose use, w/dual evaporator cooling, SS door, thin handle, white cabinet

Highlights:

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" wide spaces

Professional look with a durable stainless steel wrapped door and sleek handle

Improved temperature performance with our unique dual evaporator cooling

Product Features:

| | |
|------------------------------|--|
| ADA compliant | 32" high to fit under lower ADA compliant counters |
| Built-in capable | Make the best use of space by installing your appliance under the counter |
| Fully finished white cabinet | Allows the unit to be used freestanding |
| Slim undercounter dimensions | Less than 24" wide with a generous storage capacity |
| Stainless steel door | Durable 304 grade wrapping |
| Professional handle | Thin 14mm diameter on vertical stainless steel handle |
| Dual evaporator | Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators |
| Cycle defrost | This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment |
| Zero degree freezer | Static manual defrost freezer section offers more stability |

CT66JBISSHVADA Specifications:

| Overview | |
|----------------------------|-----------------|
| Height | 32.0" |
| Height to Hinge Cap | 32.25" |
| Width | 23.63" |
| Depth | 23.5" |
| Depth with Handle | 25.63" |
| Depth with door at 90° | 45.63" |
| Capacity | 5.1 cu.ft. |
| Defrost Type | Cycle |
| Door | Stainless Steel |
| Cabinet | White |
| US Electrical Safety | UL |
| Canadian Electrical Safety | ULC |
| Amps | 1.3 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Shipping Weight | 148.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |

| Refrigerator-Freezer | |
|----------------------------------|--------------------|
| Door Swing | RHD |
| Reversible | Factory Reversible |
| Crisper Qty | 1 |
| Crisper Finish | Transparent |
| Crisper Cover | Wire |
| Refrigerator - Interior Height | 19.5" |
| Refrigerator - Interior Width | 20.5" |
| Refrigerator - Interior Depth | 17.0" |
| Refrigerator - Shelf Type | Wire |
| Refrigerator - Shelf Qty | 2 |
| Refrigerator - Full Door Shelves | 3 |
| Freezer - Interior Height | 5.0" |
| Freezer - Interior Width | 19.0" |
| Freezer - Interior Depth | 11.5" |
| Adjustable Shelves | Yes |
| Interior Light | Yes |

| | |
|------------------------|----------|
| Thermostat Type | Dial |
| Fan Type | Exterior |
| Freon | R134a |
| Freon Amount | 2.6 |
| High Side PSI | 285.0 |
| Low Side PSI | 70.0 |
| Level Legs | 4 |
| Compressor Step Height | 7.0" |
| Compressor Step Width | 20.5" |
| Compressor Step Depth | 5.0" |

