

CT66JCSSADA



32" x 23.63" x 23.5" (H x W x D)

Built-in undercounter ADA compliant refrigerator-freezer for general purpose use, w/dual evaporator cooling, cycle defrost, and fully wrapped SS exterior

Highlights:

32" height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use under counters in 24 inch wide spaces

Complete stainless steel exterior

Improved temperature performance with our unique dual evaporator cooling

Product Features:

ADA compliant	32" high to fit under lower ADA compliant counters
Built-in capable	Make the best use of space by installing your appliance under the counter
Fully finished cabinet	Allows the unit to be used freestanding
Slim undercounter dimensions	Less than 24" wide with a generous storage capacity
Complete stainless steel exterior	Fully wrapped in 304 grade stainless steel
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Cycle defrost	This system utilizes user-friendly automatic defrost operation in the fresh food section and efficient manual defrost operation in the freezer compartment
Zero degree freezer	Static manual defrost freezer section offers more stability
Dual evaporator	Our unique and efficient design separately cools the refrigerator while maintaining zero degrees in the freezer with two evaporators

CT66JCSSADA Specifications:

Overview	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.5"
Capacity	5.1 cu.ft.
Defrost Type	Cycle
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator-Freezer	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Refrigerator - Interior Height	19.5"
Refrigerator - Interior Width	20.5"
Refrigerator - Interior Depth	17.0"
Refrigerator - Shelf Type	Wire
Refrigerator - Shelf Qty	2
Refrigerator - Full Door Shelves	3
Freezer - Interior Height	5.0"
Freezer - Interior Width	19.0"
Freezer - Interior Depth	11.5"
Adjustable Shelves	Yes
Interior Light	Yes
Thermostat Type	Dial
Freon	R134a
Freon Amount	2.6
High Side PSI	285.0
Low Side PSI	70.0

Compressor Step Height
Compressor Step Width
Compressor Step Depth

