

# Countertop Display Refrigerators



#### Standard Features



- Choice Model CTR2.68LD with illuminated header display or model CTR3.75 with extra capacity.
- Adjustable Thermostat Temperature can be adjusted between 34°F and 45°F.
- Energy Efficient Double pane thermal glass door with strong magnetic gasket.
- Impulse Sales Merchandise packaged food & beverages.
- ETL Sanitation Conforms To NSF 7 Standard.
- Durable Black Powder Coated Exterior Finish.
- Bright Interior Merchandise Lighting.
- Adjustable PVC Coated Wire Shelves.
- Secure Built-In Door Lock.

Specifications subject to change without notice.




# **Countertop Display Refrigerators**


### **Models & Dimensions**



#### CTR2.68LD Refrigerator with Illuminated Header



#### CTR3.75 Five Shelf Refrigerator



## **Options**

Additional Shelves For CTR2.68LD ....... Part # 08725 Additional Shelves For CTR3.75 ....... Part # 08727 Custom display graphics are available for CTR2.68LD at an additional charge, please contact Cecilware marketing for more information.



<b>Specifications</b>							
Model	Cubic Ft.	Shelves	Temp.	НР	Dimensions W x D x H	Electrical	Ship Weight
CTR2.68LD	2.7	4	34°F - 45°F	1/8	18" x 18¾" x 36½"	120V, .09KW, 1.8A	90 lbs.
CTR3.75	3.8	5	34°F - 45°F	1/8	18¾" x 18" x 33¼"	120V, .09KW, 2A	85 lbs.

Electrical: Cord & plug set included, Nema plug 5-15P. Refrigerant: R-134a. Finish: Black.

Specifications subject to change without notice.

