

# FF6B



33.25" x 23.63" x 23.5" (H x W x D)

Freestanding counter height all-refrigerator for general purpose use, with automatic defrost operation and black exterior

## Highlights:

Includes adjustable glass shelves for flexible storage

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

Automatic defrost ensures minimum user maintenance

Door racks provide convenient storage options

## Product Features:

Fully finished black cabinet	Allows the unit to be used freestanding
Slim counter height dimensions	Our unique 24" wide models offer full capacity in a slim fit
Automatic defrost	Reduced maintenance with auto defrost system
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior
One piece interior liner	Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Adjustable glass shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Crisper	Get the longest life and best taste out of produce by storing greens in a convenient slide drawer
Door storage	Store large bottles right on the door for easy access
Interior light	Automatically illuminates when you open the door

**FF6B Specifications:**

Overview	
Height	33.25"
Height to Hinge Cap	33.25"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.13"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Black
Cabinet	Black
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	102.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Glass
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"

Interior Depth	17.0"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

