

# FF6BISSTBADA



32" x 23.63" x 23.63" (H x W x D)

ADA compliant all-refrigerator for built-in general purpose use, auto defrost w/stainless steel wrapped door, towel bar handle, and white cabinet

## Highlights:

32 inch height fits under lower ADA compliant counters

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

Includes door storage and adjustable shelves

## Product Features:

ADA compliant	32 inch height fits under standard ADA counters
Slim undercounter dimensions	Less than 24 inches wide with a full 5.5 c.f. capacity
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished white cabinet	Allows the unit to be used freestanding
Stainless steel wrapped door	Durable design with lasting elegance
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Automatic defrost	Reduced maintenance with auto defrost system
One piece interior liner	Easy clean-up with a seamless liner that won't hold a mess in hidden crevices
Hidden evaporator	Cold wall design with hidden evaporator and seamless interior

**FF6BISSTBADA Specifications:**

<b>Overview</b>	
Height	32.0"
Height to Hinge Cap	32.25"
Width	23.63"
Depth	23.63"
Depth with Handle	26.13"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
<b>Refrigerator Features</b>	
Door Swing	RHD
Reversible	Factory Reversible
Crisper Qty	1
Crisper Finish	Opaque
Crisper Cover	Glass
Shelf Type	Wire
Shelf Qty	3
Full Door Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
<b>Dimensions</b>	
Interior Height	27.75"

Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"
Compressor Step Depth	6.0"

