

# FF7LBISSHH



33.5" x 23.63" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, auto defrost w/lock, SS door, horizontal handle, and white cabinet

## Highlights:

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel wrapped door includes horizontal handle for a professional look

Full 5.5 cu.ft. capacity inside a convenient 24" footprint

## Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Built-in capable	Make the best use of space by installing your appliance under the counter and flush with other cabinets
Fully finished cabinet	Allows the refrigerator to be used as a freestanding model
Factory installed lock	Keyed lock for a secure interior
Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Stainless steel wrapped door	Durable design with lasting elegance
Professional horizontal handle	Brushed stainless steel handle with a thin 14mm diameter is mounted horizontally across the door for a sleek look
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up
Automatic defrost	Reduced user maintenance with automatic defrost

**FF7LBISSH Specifications:**

Overview	
Height	33.5"
Width	23.63"
Depth	23.5"
Depth with Handle	25.13"
Depth with door at 90°	46.0"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	115.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"
Compressor Step Width	20.0"

Compressor Step Depth

