

FF7LCSS



33.25" x 23.75" x 23.5" (H x W x D)

Commercially listed built-in undercounter all-refrigerator for general purpose use, auto defrost w/SS exterior and front lock

Highlights:

Commercially approved for use in foodservice establishments

Flexible design allows built-in or freestanding use in 24" spaces

Stainless steel wrapped exterior, with our signature towel bar handle

Factory-installed lock provides security you can count on

Product Features:

Commercially approved	ETL-S listed to NSF-7 Standards for use in commercial establishments
Slim undercounter dimensions	Less than 24 inches wide to fit tight spaces
Built-in capability	Make the best use of space by installing your refrigerator under the counter and flush with other cabinets
Fully finished cabinet	Allows the refrigerator to be used freestanding
Complete stainless steel exterior	Durable construction with modern style
Professional towel bar handle	Curved handle in brushed stainless steel offers a sturdy grip with professional elegance
Automatic defrost operation	Reduced user maintenance with automatic defrost
Front-mounted lock	Keyed lock for a secure interior
Adjustable shelves	Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up

FF7LCSS Specifications:

Overview	
Height	33.25"
Height to Hinge Cap	34.75"
Width	23.75"
Depth	23.5"
Depth with Handle	25.25"
Depth with door at 90°	45.5"
Capacity	5.5 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	ETL-S
Amps	1.3
Shipping Weight	143.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Dial
Fan Type	Exterior
Refrigerant Type	R134a
Refrigerant Amount	1.8
High Side PSI	285.0
Low Side PSI	70.0
Level Legs Qty	4
Interior Light	Yes
Dimensions	
Interior Height	27.75"
Interior Width	20.0"
Interior Depth	17.5"
Compressor Step Height	7.0"

Compressor Step Width
Compressor Step Depth

