

FF7SSTB



33.25" x 23.63" x 23.5" (H x W x D)

Commercially listed freestanding all-refrigerator for general purpose use, auto defrost w/SS wrapped door, towel bar handle, and white cabinet

Highlights:

ENERGY STAR certified commercial refrigerator

Commercially approved for use in foodservice establishments

Automatic defrost minimizes user maintenance

Stainless steel wrapped door with professional towel bar handle adds luxury to any setting

Product Features:

| | |
|--|---|
| ENERGY STAR certified commercial performance | Meets ENERGY STAR standards as a commercial refrigerator |
| Commercially approved | ETL-S listed to NSF-7 commercial standards |
| Fully finished cabinet | Allows the refrigerator to be used as a freestanding model |
| Stainless steel wrapped door | Durable design with lasting elegance |
| Professional towel bar handle | Curved handle in brushed stainless steel offers a sturdy grip with professional elegance |
| Automatic defrost | Reduced user maintenance with automatic defrost |
| Adjustable shelves | Rearrange your refrigerator space to accommodate all shapes and sizes or remove shelves for a simple clean-up |
| One piece interior liner | Enjoy easy clean-up with a seamless liner that won't hold a mess in hidden crevices |
| Hidden evaporator | Cold wall design with hidden evaporator and seamless interior |

FF7SSTB Specifications:

| Overview | |
|----------------------------|--------------------|
| Height | 33.25" |
| Height to Hinge Cap | 33.25" |
| Width | 23.63" |
| Depth | 23.5" |
| Depth with Handle | 24.25" |
| Depth with door at 90° | 45.0" |
| Capacity | 5.5 cu.ft. |
| Defrost Type | Automatic |
| Door | Stainless Steel |
| Cabinet | White |
| US Electrical Safety | UL |
| Canadian Electrical Safety | ULC |
| Sanitation | ETL-S |
| Amps | 1.3 |
| Voltage/Frequency | 115 V AC/60 Hz |
| Shipping Weight | 113.0 lbs. |
| Parts & Labor Warranty | 1 Year |
| Compressor Warranty | 5 Years |
| Refrigerator Features | |
| Door Swing | RHD |
| Reversible | Factory Reversible |
| Shelf Type | Wire |
| Shelf Qty | 3 |
| Adjustable Shelves | Yes |
| Thermostat Type | Dial |
| Fan Type | Exterior |
| Refrigerant Type | R134a |
| Refrigerant Amount | 1.8 |
| High Side PSI | 285.0 |
| Low Side PSI | 70.0 |
| Level Legs Qty | 2 |
| Interior Light | Yes |
| Dimensions | |
| Interior Height | 27.75" |
| Interior Width | 20.0" |
| Interior Depth | 17.5" |

| | |
|------------------------|-------|
| Compressor Step Height | 7.0" |
| Compressor Step Width | 20.0" |
| Compressor Step Depth | 6.0" |

