



SBC635MOSHH



49" x 24" x 25" (H x W x D)

Freestanding residential outdoor beer dispenser, auto defrost with digital thermostat, stainless steel wrapped exterior, and horizontal handle

Highlights:

Weatherproof construction allows safe use in the outdoors

Full-sized capacity to hold half, quarter, 1/6 or mini kegs

Digital thermostat lets you set the perfect temperature for any brew


304 grade stainless steel wrapped cabinet and door ensure lasting luxury

Product Features:

Outdoor beer dispenser	Meets UL guidelines for use in the outdoors, with weatherproof construction and a sealed back
Full-sized capacity	Large 5.6 cu.ft. interior accepts half, quarter, and mini kegs
Tap Kit included	Includes a 5 lb. CO2 tank and regulator, draft arm, Sankey American dual tap, and connection hardware
Digital thermostat	Electronic controls ensure easy temperature management, with an external readout in Celsius or Fahrenheit
Stainless steel wrapped exterior	Weatherproof construction on the exterior cabinet, door, and top
Professional handle	Thin (14mm diameter) stainless steel handle mounted horizontally for a sleek look that matches many popular styles of cabinetry
Automatic defrost	Reduced user maintenance with auto defrost operation
Ideal beer temperature	Operates between 33° and 50°F to keep a variety of beers stored at just the right serving temperature
Reversible door	User-reversible door swing for added flexibility



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com



SBC635MOSHH Specifications:

Overview	
Height	49.0"
Width	24.0"
Width with Door Open	25.25"
Depth	25.0"
Depth with door at 90°	47.0"
Capacity	5.6 cu.ft.
Defrost Type	Automatic
Door	Stainless Steel
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Energy Usage/Year	310.0kWh/year
Amps	0.86
Voltage/Frequency	115 V AC/60 Hz
Weight	150.0 lbs.
Shipping Weight	180.0 lbs.
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Beer Dispenser	
Door Swing	RHD
Reversible	Yes
Tap Kit	Yes
Number of Taps	1
Thermostat Type	Digital
Refrigerant	R600a
Refrigerant Amount	1.13 oz.
High Side PSI	250.0
Low Side PSI	110.0
Inter Height	28.0"
Interior Width	20.5"
Interior Depth	19.0"
Wheel Qty	4
Surface	Stainless Steel
Temperature Range	33° to 50° F



SUMMIT APPLIANCE DIVISION FELIX STORCH, INC.

770 Garrison Avenue, Bronx, NY 10474 USA TEL 718-893-3900 FAX 844-478-8799 info@summitappliance.com  www.summitappliance.com