

# RATCHETING PLASTIC TUBING CUTTERS



### Rugged and Durable

An ergonomic, cast-aluminum body and stainless steel blade increase life and durability.



### Comfortable Grip

A rubberized handle makes it easier to use in wet and dirty environments.



### Easy to Open and Close

A conveniently placed release button allows for true one-handed operation, while a locking tab secures the blade in place.

Ratcheting Plastic Tubing Cutter  
1-5/8" MAX OD  
1885393



### Rugged and Durable

An ergonomic, cast-aluminum body and high-carbon steel blade increase life and durability.



### Easy to Open

Simply pull both handles apart to quickly start the next cut.

Ratcheting Plastic Tubing Cutter  
2-3/8" MAX OD  
1885395



## Product Specifications

Item Number	1885393
Product Description	RPTC158
Diameter	1-5/8" MAX OD

### Dimensions

Length	9"
Width	1-1/8"
Height	4-1/8"
Weight	1.0 lbs.

### Replacement Blade

Item Number	1885394
Product Description	RPTC158RB Rat TC Rep Blade



Scan this QR Code for blade change instructions for the 1-5/8" Ratcheting Plastic Tubing Cutter.

## Product Specifications

Item Number	1885395
Product Description	RPPTC238
Diameter	2-3/8" MAX OD

### Dimensions

Length	13-1/8"
Width	1-1/3"
Height	6"
Weight	2.5 lbs.

### Replacement Blade

Item Number	1885396
Product Description	RPTC238RB Rat TC Rep Blade



Scan this QR Code for blade change instructions for the 2-3/8" Ratcheting Plastic Tubing Cutter.