

CU2W

Wet Location LED Emergency Light

FEATURES

- Emergency unit for wet location or light industrial applications
- UV stable thermoplastic grey housing available
- Quick installation with fully adjustable lamp-heads
- LED Lamps with a life-cycle of more than 10 years
- Dual-voltage 120 or 277V AC input
- Provided with water-proof test switch and AC-On indicator
- Remote capacity or extended runtime standard
- Long-life Nickel Cadmium battery with fully automatic charger
- UL 924 Wet Location Listed



FLOODLIGHTS

ORDERING INFORMATION

CATALOG NUMBER	DESCRIPTION
----------------	-------------

CU2WG	Wet Location LED emergency light, Dual-Head Fully Adjustable, Grey Finish, Remote Capacity, 120/277 Input, 1.9 watts
--------------	--

CU2WB	Wet Location LED emergency light, Dual-Head Fully Adjustable, Black Finish, Remote Capacity, 120/277 Input, 1.9 watts
--------------	---

Note: Unit will only power 1 each Compass CWRD or 2 each CWRS remotes

MATCHING REMOTE FIXTURES

MODEL	DESCRIPTION
-------	-------------

CWRS	LED Outdoor Remote, Single
-------------	----------------------------

CWRD	LED Outdoor Remote, Double
-------------	----------------------------

ACCESSORIES


MODEL	DESCRIPTION
-------	-------------

WGEL	Wireguard- 8" H X 20" W X 8" D
-------------	--------------------------------

ELECTRONICS

- 90 minute emergency operation with 1 double or 2 single remotes
- Test switch and LED AC-on indicator light

CWRS



Single Carton Weight: 7.5 lbs.
Master Carton Quantity: 4 each

