




IRONguard

Protecting Your People

Portable Safety Zone

Portable Safety: Anywhere...anytime.

- Quickly create a safe and complete visual barrier zone in virtually unlimited indoor applications.
- Easily transportable.
- Simple setup and take-down.
- Slim design takes little space and allows for easy storage.



CREATE A BARRIER FOR INSPECTIONS



SECURE A TEMPORARY HAZARDOUS AREA



PROTECT MAINTENANCE AND SERVICE PERSONNEL

PORTABLE SAFETY ZONE FEATURES

- The Portable Safety Zone design utilizes features representing the breakthrough in 'ease of use' barrier systems.
- Light weight and balanced for easy transportation by one operator.
- Robust construction in 'safety orange' powder coated steel.
- The Portable Safety Zone comes complete with 100' safety orange fencing, 4 posts, 4 rubber base pads and 4 magnetic fence clips.
- The unique fence locking system ensures a sturdy fence assembly.
- Easily fits through 30" doorways.
- Suitable for both indoor & outdoor applications on smooth surfaces.
- Optional LED beacons create a clear awareness of the Portable Safety Zone location in low light conditions.



PORTABLE SAFETY ZONE OPERATION

- Manually transport the Portable Safety Zone to the required location on the integrated mobile frame.
- Position the posts/base pads and/or magnetic clips at the desired location.
- Unlock the fence and extract around the posts.
- Lock the fence in position.
- Follow these steps in reverse to retract the fence and move to another location.



OVERALL SIZE: 27" DEEP X 25" WIDE X 54" HIGH.
APPROXIMATE WEIGHT IS 256LBS.

MORE SAFETY SOLUTIONS:



Toll-Free Phone: 1-866-828-6737
Toll-Free Fax: 1-844-899-0088
ironguardsafety.com info@ironguardsafety.com

Many IronGuard Safety Products are trademarked and covered by U.S. or international patents. Products may change without prior notice.

Form [PSZ-SLM EN HI - IG-L-201503]