

JDP-20MF, 20" FLOOR DRILL PRESS 115/230V 1PH

354170

Accuracy, stability and versatility are the benchmark features of the JET 15" and 20" Drill Presses. This high quality line of JET Drill Presses offer a greater range in spindle speeds than other machines of this class. JET backs their machines with the industry-leading Two Year Warranty.



FEATURES

- Hinged metal belt and pulley cover
- Quick adjustment motor mount for rapid changing of spindle speeds
- Rotating, 45° tilting, crank operated worktable with release clamp
- On/off switch located on front of drill press head
- 1/2" diameter external depth stop with three nut locking feature for quick adjustment
- Adjustable tension spindle return spring
- Spindle is supported by high quality bearings
- Drill chuck and key included
- Telescoping safety spindle guard



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

JDP-20MF, 20" FLOOR DRILL PRESS 115/230V 1PH

354170

SPECIFICATIONS

Style (Type)	Variable
Drills to Center of Circle (in.)	20
Drilling Capacity Cast Iron (In.)	1
Drilling Capacity Mild Steel (In.)	3/4
Distance Column to Spindle (In.)	10
Number of Spindle Speeds	12
Range of Spindle Speeds (RPM)	150 - 4,200
Column Diameter (In.)	3-3/8
Spindle Taper (In. x TPI)	MT-3
Spindle Travel (In.)	4-5/8
Spindle Distance to Base (In.)	46-3/4
Spindle Distance to Table (Max.) (In.)	29-1/8
Table Size (L x W) (In.)	18-1/2 x 16
Table Travel (In.)	21-1/2
T-Slots Number and Size (In.)	6 & 1/2
T-Slot Centers (In.)	3-1/2
Work Table Weight Capacity (Lbs.)	80



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE