

HVBS-710G, 7" X 10-1/2" HORIZONTAL/VERTICAL MITERING GEARED HEAD BANDSAW

413452

JET Mitering Horizontal bandsaws unique design features a swiveling head while the base remains stationary. This allows the stock to remain same position while making accurate crosscuts and miters. Backed by the industry leading two year warranty, JET Mitering Bandsaws are built to last and deliver precision results.



FEATURES

- UL Listed Motor
- Mitering head swivels to cut any angle 0° - 45° while the work piece remains secured
- Hardened and ground drive shaft and worm gears transmit maximum torque to blade wheels
- Fully adjustable hydraulic downfeed system
- Heavy-duty cast iron saw bow and bed
- Large 8" wheels and handle for easy movement
- Quick-positioning vise with fully adjustable jaws
- Built-in, self propelled blade brush extends blade life
- Vertical work table
- Coolant system
- Adjustable material stop
- 3/4" Bi-Metal blade



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

HVBS-710G, 7" X 10-1/2" HORIZONTAL/VERTICAL MITERING GEARED HEAD BANDSAW

413452

SPECIFICATIONS

Cutting Capacity (W x D) (In.)	7 x 10-1/2
Round at 90 Degrees (In.)	7
Round at 45 Degrees (In.)	4
Rectangle at 90 Degrees (In.)	7 x 10-1/2
Rectangle at 45 Degrees (In.)	4-3/4 x 4
Vise Swivels (Deg.)	45°
Head Movement (Deg.)	45°
Blade Size (In.)	3/4 x .035 x 93
Blade Length (In.)	93-5/8
Blade Wheel Diameter (In.)	11-3/4
Blade Speed (SFPM)	145, 200, 245
Bed Height (In.)	23
Motor (HP)	1 HP, 115/230V, 1Ph
Drive	Geared Head
Overall Dimensions (L x W x H) (In.)	51 x 22-1/2 x 41
Weight (Lbs.)	401



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE