

HBS-812G, 8" X 12" HORIZONTAL/VERTICAL GEARED HEAD BANDSAW

413460

Innovative and built to last; that's how customers describe the latest addition to the JET line of saws. Easy speed change, quick lock vise and large 8" wheels enhance the convenience of this rugged machine. It is everything you expect from a JET saw.



FEATURES

- UL Listed motor
- Heavy-duty geared head transmission for quick speed changes
- Heavy-duty cast iron saw bow and head
- Hardened and ground worm gear
- Large 8" wheels and handle for easy movement
- Quick-positioning vise swivels to 45°, reducing set up time
- Built-in, self propelled blade brush extends blade life
- Vertical work table
- Coolant system
- Adjustable material stop
- 3/4" Bi-Metal blade



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

HBS-812G, 8" X 12" HORIZONTAL/VERTICAL GEARED HEAD BANDSAW

413460

SPECIFICATIONS

Cutting Capacity (W x D) (In.)	8 x 12
Round at 90 Degrees (In.)	8
Round at 45 Degrees (In.)	5
Rectangle at 90 Degrees (In.)	8 x 11-1/4
Rectangle at 45 Degrees (In.)	5 x 8
Vise Swivels (Deg.)	45°
Blade Speeds (SFPM)	145, 200, 245
Blade Wheel Diameter (In.)	11-1/2
Blade Length (In.)	93
Blade Size (In.)	3/4 x .035 x 93
Bed Height (In.)	43
Motor (HP)	1 HP, 115/230V, 1Ph
Weight (Lbs.)	308
Overall Dimensions (L x W x H) (In.)	51 x 19 x 43



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE