

J-4200A, 6 X 48 INDUSTRIAL COMBINATION BELT AND DISC FINISHING MACHINE 115V 1PH

414551

High-speed precision and amazing versatility. This rugged piece of equipment has a belt that operates at any angle, and conforms to curves, angles or circular finishing and grinding operations. Machinists who take great pride in their work prefer the JET Industrial Combination Belt & Disc Finishing Machine



FEATURES

- For added safety, the J-4200A follows strict guidelines and electrical requirements to be certified by CSA Group
- Plain and compound miters are easily obtained by using the standard die cast aluminum miter gauge
- Fully machined, balanced disc
- Belt operates at any angle
- Removable upper belt guard for contour finishing
- Completely enclosed drums and guarded sanding belt
- Adjustable heavy-duty cast iron removable platen
- Variable position locks
- Belt head adjusts vertically and horizontally
- Large cast iron slotted table
- Adjustable dust collector and dust chute
- Heavy-duty one-piece steel stand
- 60 grit belt and disc standard on machine
- Miter gauge included



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

J-4200A, 6 X 48 INDUSTRIAL COMBINATION BELT AND DISC FINISHING MACHINE 115V 1PH

414551

SPECIFICATIONS

Disc Diameter (In.)	12
Disc Speed (RPM)	1,960
Belt Size (W x L) (In.)	6 x 48
Belt Speed (SFPM)	2,850
Disc Table Size (L x W) (In.)	12 x 16-3/8
Disc Table Tilt (Deg.)	45 Out, 20 In
Table Slots (In.)	3/8 & 3/4
Belt Table Tilt (Deg.)	45 Out, 20 In
Belt Table Size (In.)	7-3/8 x 14-3/4
Motor (HP)	1-1/2 HP, 115V, 1 Ph
Overall Dimensions (L x W x H) (In.)	29 x 19 x 58
Weight (Lbs.)	250



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE