

JTM-4VS-1 MILL WITH 3-AXIS ACU-RITE 200S DRO (QUILL) WITH X AND Y-AXIS POWERFEEDS

690068

Constructed using the Meehanite® casting process, JET Variable Speed Milling Machines provide consistent and reliable operation. Precision bored and honed milling heads ensure quality cuts, and the three-stage power downfeed with automatic stop makes the JET Variable Speed Milling Machines easy to use. Available in single or three phase power configurations, the JET JTM-4VS Series mills are backed by the industry leading two year full service and parts warranty



FEATURES

- Meehanite Castings
- Precision bored and honed milling head
- Large diameter quill is chromed
- High precision Class 7 spindle bearings
- Chrome plated motor shaft with lower bearing support
- Spindle head is internally cooled
- Heavy duty splined motor drive
- One piece quill pinion and shaft
- Three stage power downfeed with automatic stop
- Heavy duty spindle brake
- Locks on all movable surfaces
- Precision hardened and ground ways and table
- Adjustable gibs throughout
- Internal coolant tank built into casting base for use with coolant system (coolant pump not included)
- Tolerance test sheet included
- One shot lubrication system
- Way covers
- Draw bar
- Tool box with tools



JET RED ASSURANCE 2-YEAR WARRANTY

JET warrants every product it sells. If one of our tools needs service or repair, one of our Authorized Service Centers located throughout the United States can give you quick service. In most cases, any of these JPW Industries Authorized Service Centers can authorize warranty repair, assist you in obtaining parts, or perform routine maintenance and major repair on your JET tools. For the name of an Authorized Service Center in your area call 1-800-274-6848.

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

JTM-4VS-1 MILL WITH 3-AXIS ACU-RITE 200S DRO (QUILL) WITH X AND Y-AXIS POWERFEEDS

690068

SPECIFICATIONS

| | |
|--|----------------------|
| Spindle Taper (In. x TPI) | R-8 |
| Digital Readout | ACU-RITE 200S |
| Number of Axis | 3 (Quill) |
| Powerfeed | X and Y-Axis |
| Table Size (L x W) (In.) | 9 x 49 |
| Quill Diameter (In.) | 3-3/8 |
| Number of Spindle Speeds | Variable |
| Range of Spindle Speeds (RPM) | 60 - 4,200 |
| Quill Down Feed Rates (IPR) | .0015 - .003 - .006 |
| Spindle Travel (In.) | 5 |
| Head Movement (Deg.) | 90° R & L, 45° F & B |
| Max Distance Spindle to Table (In.) | 17-1/2 |
| Distance Spindle to Column (Max.) (In.) | 19 |
| Distance Spindle to Column (Min.) (In.) | 4-1/2 |
| Collet Capacity | 1/8 - 7/8 |
| Table Longitudinal Travel (In.) | 34 |
| Table Longitudinal Travel With Powerfeed (In.) | 28-3/4 |



STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

JTM-4VS-1 MILL WITH 3-AXIS ACU-RITE 200S DRO (QUILL) WITH X AND Y-AXIS POWERFEEDS

690068

FULL SERIES

| STOCK NO | MODEL NO | SPINDLE TAPER (IN. X TPI) | DIGITAL READOUT | NUMBER OF AXIS | POWERFEED | POWER DRAW BAR |
|----------|----------|---------------------------|-----------------|----------------|-----------------|----------------|
| 690182 | JTM-4VS | R-8 | | | | |
| 690183 | JTM-4VS | R-8 | | | X-Axis | |
| 690008 | JTM-4VS | R-8 | | | X and Y-Axis | |
| 690009 | JTM-4VS | R-8 | | | X and Y-Axis | Pneumatic |
| 690013 | JTM-4VS | R-8 | | | X, Y and Z-Axis | |
| 690119 | JTM-4VS | R-8 | | | | |
| 691088 | JTM-4VS | R-8 | ACU-RITE VUE | | | |
| 690401 | JTM-4VS | R-8 | ACU-RITE VUE | 2 | X-Axis | |
| 690265 | JTM-4VS | R-8 | ACU-RITE VUE | 2 | X-Axis | |
| 690415 | JTM-4VS | R-8 | ACU-RITE VUE | 2 | X-Axis | Pneumatic |
| 690420 | JTM-4VS | R-8 | ACU-RITE VUE | 2 | X and Y-Axis | |
| 690417 | JTM-4VS | R-8 | ACU-RITE VUE | 2 | X, Y and Z-Axis | |
| 690416 | JTM-4VS | R-8 | ACU-RITE VUE | 3 (Quill) | X and Y-Axis | |
| 690408 | JTM-4VS | R-8 | ACU-RITE VUE | 3 (Knee) | X-Axis | |
| 690412 | JTM-4VS | R-8 | ACU-RITE VUE | 3 (Knee) | X and Y-Axis | |
| 690418 | JTM-4VS | R-8 | ACU-RITE VUE | 3 (Knee) | X, Y and Z-Axis | |
| 690202 | JTM-4VS | R-8 | ACU-RITE 200S | 2 | | |
| 690107 | JTM-4VS | R-8 | ACU-RITE 200S | 2 | X-Axis | |
| 690125 | JTM-4VS | R-8 | ACU-RITE 200S | 2 | X-Axis | Pneumatic |
| 690098 | JTM-4VS | R-8 | ACU-RITE 200S | 2 | X and Y-Axis | |
| 690230 | JTM-4VS | R-8 | ACU-RITE 200S | 2 | X and Y-Axis | Pneumatic |
| 690099 | JTM-4VS | R-8 | ACU-RITE 200S | 2 | X, Y and Z-Axis | |

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

JTM-4VS-1 MILL WITH 3-AXIS ACU-RITE 200S DRO (QUILL) WITH X AND Y-AXIS POWERFEEDS

690068

FULL SERIES

| STOCK NO | MODEL NO | SPINDLE TAPER (IN. X TPI) | DIGITAL READOUT | NUMBER OF AXIS | POWERFEED | POWER DRAW BAR |
|----------|-----------|---------------------------|-----------------|----------------|-----------------|----------------|
| 690221 | JTM-4VS | R-8 | ACU-RITE 200S | 3 (Quill) | X-Axis | |
| 690251 | JTM-4VS | R-8 | ACU-RITE 200S | 3 (Quill) | X-Axis | Pneumatic |
| 690140 | JTM-4VS | R-8 | ACU-RITE 200S | 3 (Quill) | X and Y-Axis | |
| 690139 | JTM-4VS | R-8 | ACU-RITE 200S | 3 (Quill) | X and Y-Axis | Pneumatic |
| 690141 | JTM-4VS | R-8 | ACU-RITE 200S | 3 (Quill) | X and Y-Axis | |
| 690153 | JTM-4VS | R-8 | ACU-RITE 200S | 3 (Quill) | X, Y and Z-Axis | Pneumatic |
| 690400 | JTM-4VS | R-8 | ACU-RITE 200S | 3 (Knee) | 3 (Knee) | Pneumatic |
| 690301 | JTM-4VS | R-8 | ACU-RITE 300S | 2 | X-Axis | |
| 690302 | JTM-4VS | R-8 | ACU-RITE 300S | 2 | X and Y-Axis | |
| 690430 | JTM-4VS | R-8 | ACU-RITE 300S | 3 (Knee) | X, Y and Z-Axis | Pneumatic |
| 691200 | JTM-4VS | R-8 | Newall DP700 | 2 | | |
| 690087 | JTM-4VS | R-8 | Newall DP700 | 2 | X-Axis | |
| 690069 | JTM-4VS | R-8 | Newall DP700 | 2 | X-Axis | Pneumatic |
| 691201 | JTM-4VS | R-8 | Newall DP700 | 2 | X and Y-Axis | |
| 691202 | JTM-4VS | R-8 | Newall DP700 | 3 (Quill) | | |
| 690090 | JTM-4VS | R-8 | Newall DP700 | 2 | X-Axis | |
| 691203 | JTM-4VS | R-8 | Newall DP700 | 3 (Quill) | X and Y-Axis | |
| 691170 | JTM-4VS | R-8 | Newall DP700 | 3 (Quill) | X, Y and Z-Axis | Pneumatic |
| 691232 | JTM-4VS | R-8 | Newall DP700 | 3 (Knee) | X-Axis | |
| 690093 | JTM-4VS | R-8 | Newall DP700 | 3 (Knee) | X, Y and Z-Axis | |
| 690094 | JTM-4VS | R-8 | Newall DP700 | 3 (Knee) | X, Y and Z-Axis | Pneumatic |
| 690180 | JTM-4VS-1 | R-8 | | | | |

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE

JTM-4VS-1 MILL WITH 3-AXIS ACU-RITE 200S DRO (QUILL) WITH X AND Y-AXIS POWERFEEDS

690068

FULL SERIES

| STOCK NO | MODEL NO | SPINDLE TAPER (IN. X TPI) | DIGITAL READOUT | NUMBER OF AXIS | POWERFEED | POWER DRAW BAR |
|----------|-----------|---------------------------|-----------------|----------------|-----------------|----------------|
| 690197 | JTM-4VS-1 | R-8 | | | X and Y-Axis | |
| 692402 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 2 | | |
| 690402 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 2 | X-Axis | |
| 690407 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 2 | X and Y-Axis | |
| 690422 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 2 | X and Y-Axis | Pneumatic |
| 690410 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 3 (Quill) | X-Axis | |
| 690413 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 3 (Quill) | X and Y-Axis | |
| 690421 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 3 (Quill) | X, Y and Z-Axis | |
| 690411 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 3 (Knee) | X-Axis | |
| 690424 | JTM-4VS-1 | R-8 | ACU-RITE VUE | 3 (knee) | X, Y and Z-Axis | |
| 690179 | JTM-4VS-1 | R-8 | ACU-RITE 200S | 2 | X-Axis | |
| 690068 | JTM-4VS-1 | R-8 | ACU-RITE 200S | 3 (Quill) | X and Y-Axis | |
| 691411 | JTM-4VS-1 | R-8 | ACU-RITE 200S | 3 (Knee) | X-Axis | |
| 690303 | JTM-4VS-1 | R-8 | ACU-RITE 300S | 2 | X-Axis | |
| 690118 | JTM-4VS-1 | R-8 | ACU-RITE 300S | 3 (Quill) | X and Y-Axis | |
| 692087 | JTM-4VS-1 | R-8 | Newall DP700 | 2 | | |
| 691087 | JTM-4VS-1 | R-8 | Newall DP700 | 2 | X-Axis | |
| 692306 | JTM-4VS-1 | R-8 | Newall DP700 | 2 | X and Y-Axis | |
| 691171 | JTM-4VS-1 | R-8 | Newall DP700 | 3 (Quill) | X, Y and Z-Axis | Pneumatic |

STAND BEHIND YOUR WORK™



550+ SERVICE CENTERS NATIONWIDE

INDUSTRY-LEADING WARRANTIES

EXPERT TECHNICAL SERVICE