



## LED WALL LANTER

F9937-31

SHOWN IN -BK (BLACK)

**Description:** LED exterior wall mount, driver on board, non-dimmable

**Dimensions:** 8-1/4"W x 12-1/4"H x 5-1/2"E

**Finish:** Black

**Lens / Diffuser:** Frosted Lens

**Lamp Source:** 9W LED Integrated Luminaire with Photo Cell

**Lumens:** 700

**Color Temperature:** 4000k

**CRI:** 80

**Voltage:** 120

**Ratings:** ETL Listed, Energy Star Rated.



**SUNSET LIGHTING AND FANS / A DIVISION OF LUMINANCE**

1945 TUBEWAY AVE / CITY OF COMMERCE / CA 90040

TELEPHONE: (800) 777-4440 / FAX: (800) 866-7672 / EMAIL: [INSIDESALES@LUMINANCE.US.COM](mailto:INSIDESALES@LUMINANCE.US.COM)

WEBSITE: [WWW.LUMINANCE.US.COM](http://WWW.LUMINANCE.US.COM)