

**Explosion Proof LED Drop Light / Trouble Light -10 Watt LED - 120V AC - 50ft General Use Cord Reel**

Part #: EHL-LED-7W-GCR50

**Made in the USA**

**The Larson Electronics EHL-LED-7W-GCR50 Explosion Proof LED Drop Light / Trouble Light is U.L. approved Class 1 Division 1 & 2 Groups C and D - and is ideal for general work activities in hazardous locations requiring explosion proof protection.**

This 10 watt explosion proof LED work light from Larson Electronics produces 1050 lumens of bright white light and comes complete with 50 feet of cable within a general use cord reel. The EHL-LED-7W-GCR50 LED drop light has no ballast and the housing is constructed of non sparking aluminum which results in a very lightweight unit. This hazardous location hand lamp is Class 1, Division 1 and 2 and Class 2 Division 1 and 2 hazardous location environment approved. This explosion proof LED drop light is ideal for hazardous work areas where a ready source of easily managed lighting is desired.



100 Watt Incandescent Bulb



With the EXP-LED-7W-25

[Click Photos to Enlarge](#)[Click Photos to Enlarge](#)[Click Photos to Enlarge](#)

This 10 watt LED drop light is suitable for use in areas where petrochemical vapors and various dusts are present and projects 1050 lumens of light, which is twice the lumen per watt output of a 100 watt incandescent bulb. This unit is rated Class 1, Division 1 and comes complete with 50' of SOW 16/3 AWG cable wound inside of the retractable cord reel and can be terminated in your choice of a 5-15 straight blade plug for 110V wall outlets with ground, NEMA L5-15 twist lock plug for 125V twist lock outlets, NEMA L6-15 twist lock plug for 240V twist lock outlets, BS1363 3-blade plug for United Kingdom outlets, two pin Schuko plug for European outlets or a 1/2" NPT junction box. The junction box allows operators to bring in conduit or make their own electrical connections.

This hand lamp has a high efficiency LED bulb that requires no ballast, so the operator doesn't need to drag the ballast housing around. This can be particularly annoying when the ballast becomes entangled in the cord. This explosion proof LED hand light operates on standard 120 Volts, 60 Hz for US voltages. The light produced by this unit has a 6000k color temperature, which is much sharper and whiter than the light produced by incandescent lamps. The light produced by this lamp is ideal for close work and inspection activities where good contrast and true color representation is needed. The LED lamp in this unit runs much cooler than incandescent or fluorescent lamps, resulting in a lamp housing that remains cool to the touch and eliminates the accidental burns often encountered with incandescent drop lights.

#### Made in USA Quality

1. Federal Spec Cord.
2. Explosion Proof.
3. 10 Watt 1050 Lumen LED Lamp.
4. Rugged fabricated steel and cast aluminum construction.
5. Blue and Gray paint finish.
6. UL Class1 Div1 Class 2 Div1
7. 120 Volt Operation
8. SOOW cable.
9. Aluminum Hook for Convenient Placement.

#### Lamp Features

- 10 watt LED light produces 1050 lumens
- Non-sparking aluminum housing
- 50,000 hour LED Lamp
- Molded rubber bumper guard
- Annealed glass tube shields prevent shattering
- Integrated lamp shock absorbers prevent drop damage
- Swivel hook for hanging and hands free operation

**Specifications / Additional Information****EHL-LED-7W-GCR50****UL Listing:** United States**Dimensions (lamp):** L-16.5 " Dia-5"**Lumens:** 1050**Total Watts:** 10 watts**Voltage:** Stnd-110/115/120VAC**Color Temp:** 6000k**Mounting:** Aluminum Hook**Wiring:** 50' 16/3 AWG SOW cord w/ Cord Reel**Lamp Type:** LED**Cord Connector:** 5-15 Straight,L5-15 Twist,L6-15 Twist,UK  
BS1363,Intl Schuko, Junction Box**YOU CAN RENT THIS UNIT. CONTACT 1-800-369-6671.**

3 year warranty replacement on this LED light. After 30 days, the customer ships the failed LED light and/or LED bulb to Larson Electronics at their expense. If the failure is a manufacturer defect, we will ship a new replacement to the customer. If failure occurs within 30 days of receipt, Larson Electronics will provide a return label via email to the customer. When the failed light is returned, Larson Electronics will ship a new replacement.

**Scroll Down to Purchase- Same Day Shipping on This Light!**

**Part #: EHL-LED-7W-GCR50 (69057)**

**U.L. Ratings**

Class 1, Division 1 &amp; 2 for Groups C, D

Class II, Division 1 and 2 for Groups F, G

**Special Orders- Requirements**

Contact us for special requirements

**Toll Free:** 1-800-369-6671**Intl:** 1-903-498-3363**E-mail:** sales@larsonelectronics.com





Links (Click on the below items to view):

- [Hi-Res Image 1 - Explosion Proof LED Drop Light/Trouble Light](#)
- [Hi-Res Image 2 - Explosion Proof LED Drop Light/Trouble Light](#)
- [Hi-Res Image 3 - Explosion Proof LED Drop Light/Trouble Light](#)
- [Hi-Res Image 4 - Explosion Proof LED Drop Light/Trouble Light](#)
- [Hi-Res Image 5 - Explosion Proof LED Drop Light/Trouble Light](#)
- [Hi-Res Image 6 - Explosion Proof LED Drop Light/Trouble Light](#)
- [Hi-Res Image 7 - Explosion Proof LED Drop Light/Trouble Light](#)
- [Hi-Res Image 8 - Explosion Proof LED Drop Light/Trouble Light](#)

