

System 273 23712RB



SYSTEM 273RB-FL

23mm Binocular Stereo-Zoom Microscope with sturdy, heavy-duty, cast aluminum housing and dual boom ball-bearing boomstand. Nearly 8in. working distance (when used with a 0.5X reducing lens), 7X-45X magnification range and 0.7X-4.5X zoom range. 17W fluorescent ring light.

Old item no.: 23712RB



Electrical data

Maximum frequency (Hz)	6 0
Minimum frequency (Hz)	5 0
Maximum voltage (V)	1 2 0
Voltage from (V)	1 0 0
Total consumption (W)	1 7

Lightsource

Number of lamps	1
Lightsource	T 5
CRI and/or Color Temperature	5 6 0 0 K

Termination

Cord length (ft)	5
Mounting	Boomstand

Ballast

Type of Ballast	Multi watt HF
-----------------	---------------

Dimensions

Net weight (kg)	0
Arm length (in.)	2 6
Gross weight (lb.)	6 3

Body

Body color	Grey
Body material	Aluminum

Technical data

IP classification	2 0
-------------------	-----

Optic

Working distance (mm)	1 1 8
-----------------------	-------