

PULSAR GENERATOR INFORMATION CHECKLIST	
Product Name	Pulsar 1200W Gasoline Generator
Brand	Pulsar
Model#	PG1202S
Rated Wattage Continuous (Watts)	850
Rated Wattage Peak (Watts)	1000
Color(s)	Black & White
Generator Type	Portable Generator
Engine Make (On EPA Label)	1E47F DZHRS.0725NL
Engine Manufacturer	ZHEJIANG ROBOT POWER MACHINERY CO., LTD.
Fuel Gauge	WITHOUT
Fuel Tank Capacity (Gallons)	1.1
Generator Power Type	air cooled 2 stroke
Auto Idle Control	no
Engine Displacement (cc)	72
Wheel Kit Included	NO
Full Load Fuel Consumption (Gallons/Hour)	0.166
Run Time at 50% Load (Hours/Tank)	9
Automatic Voltage Regulation	no
Battery Charger with Cables	yes
Built-in Inverter	no
Fuel Type	nonleaded gasoline
Horse Power (hp)	2.2hp
Hours Meter	no
Low Oil Shut Off	no
Operational Volume (dB)	65
OSHA Required GFCI Outlets	no
Overload Protection	yes
Power Type	Revolving Magnetic Field
Starter Type	recoil starter
Voltage Rating (Volts)	120v
Amperage (Amps)	Rated Amps: 4A
Number of Circuits	1
Number of Output Receptacles	2
Assembly Required	yes
Muffler	yes
Product Height (in.)	12.4
Product Length (in.)	14.6
Product Width (in)	12.4
Product Weight (lb.)	36.2
Package Height (in.)	14
Package Length (in.)	16
Package Width (in)	15
Package Gross Weight (lb.)	39.68
Manufacturers Warranty	1
UL Safety Listing	no
CARB Certificate	n0
CSA Certificate	no
Energy Start Compliant	NO
EPA Approval	yes

ETL Certified	no
QA: Does this product require an MSDS Report	no
QA: Is a Prop 65 Warning Required?	no
Sensormatic Tag in Package	no
QA: UL, ETL, CSA or ARL Tested/Listed?	no