



SAFETY DATA SHEET

Issuing Date 1-June-2015

Revision Date 11-May-2015

Revision Number 1

1. Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade Name: Citrus Breeze SeBreeze Odor Absorbing Gel

Product/Sales No: FG9C8401

1.2 Relevant identified product use

Intended use: Air Freshener

1.3 Details of the manufacturer/supplier of the safety data sheet

Manufactured for: Rubbermaid Commercial Products LLC
3124 Valley Ave.
Winchester, VA 22601
800-347-9800

1.4 Emergency telephone number

(800) 535-5053 Infotrac

2. Hazards Identification

2.1 Classification of the substance or mixture

This mixture has not been tested as a whole. The effects, listed below, are based on evaluation of individual components in accordance with the provisions of the regulation(s) noted below.

Classification according to GHS Regulation (EC) No 1272/2008

Acute Toxicity Dermal, Category 5	H313: May be harmful in contact with skin
Sensitization, Skin, Category 1B	H317: May cause an allergic skin reaction Eye Damage/Eye
Irritation, Category 2A	H319: Causes serious eye irritation
Acute Toxicity Inhalation, Category 5	H333: May be harmful if inhaled
Aquatic Chronic Toxicity, Category 3	H412: Harmful to aquatic life with long lasting effects

Classification EU (67/548/EEC, 199/45/EC)

Xi	Irritant
	R43: May cause sensitization by skin contact
Xn	Harmful
	R65: Harmful: may cause lung damage if swallowed.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms



Signal Word: Warning

Hazard statements

H313	May be harmful in contact with skin
H317	May cause an allergic skin reaction
H319	Causes serious eye irritation
H333	May be harmful if inhaled
H412	Harmful to aquatic life with long lasting effects

Precautionary Statements

Prevention:

P264	Wash hands thoroughly after handling
P272	Contaminated work clothing should not be allowed out of the workplace
P273	Avoid release to the environment

Response:

P302 + P352	IF ON SKIN: Wash with soap and water
P304 + P312	IF INHALED: Call a POISON CENTER or doctor/physician if you feel unwell
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes Remove contact lenses if present and easy to do. Continue rinsing
P333 + P313	If skin irritation or a rash occurs: Get medical advice/attention
P337 + P313	If eye irritation persists: Get medical advice/attention
P363	Wash contaminated clothing before reuse

2.3 Other Hazards

No data available

3. Composition/Information on Ingredients

3.1 Mixtures

This product is a complex mixture of ingredients, which contains among others the following substance(s), presenting a health or environmental hazard within the meaning of the UN Globally Harmonized System of Classification and Labeling of Chemicals (GHS):

CAS# Ingredient	EC#	Conc. Range	GHS Classification	EU Classification
64742-48-9	265-150-3	40 - 50 %	H304	Xn - R65
<i>Naphtha, petroleum, hydrotreated heavy</i>				
90622-46-1	292-448-0	30 - 40 %	H304	Xn - R65
<i>Alkanes, C14-C16</i>				
112-31-2	203-957-4	5 - 10 %	H227; H319; H401; H412	N - R51/53
<i>Decanal</i>				
5392-40-5	226-394-6	2 - 5 %	H313; H315; H317; H319; H401	Xi - R38, R43
<i>Citral</i>				
124-13-0	204-683-8	1 - 2 %	H226; H315; H319; H401; H402; H411	R10; N - R51/53; Xi - R36, R38
<i>Octanal</i>				

See Section 16 for full text of GHS classification codes

Total Hydrocarbon Content (% w/w) = 77.98

4. First Aid Measures

4.1 Description of first aid measures

Inhalation:	Remove from exposure site to fresh air and keep at rest. Obtain medical advice.
Eye Exposure:	Flush immediately with water for at least 15 minutes. Contact physician if symptoms persist.
Skin Exposure:	Remove contaminated clothes. Wash thoroughly with water (and soap). Contact physician if symptoms persist.
Ingestion:	Rinse mouth with water and obtain medical advice.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms:	No data available
Risks:	Refer to Section 2.2 "Hazard Statements"

4.3 Indication of any immediate medical attention and special treatment needed

Treatment:	Refer to Section 2.2 "Response"
-------------------	---------------------------------

5. Fire-Fighting measures

5.1 Extinguishing media

Suitable:	Carbon dioxide (CO ₂), Dry chemical, Foam
Unsuitable	Do not use a direct water jet on burning material

5.2 Special hazards arising from the substance or mixture

During firefighting: Water may be ineffective

5.3 Advice for firefighters

Further information: Standard procedure for chemical fires

6. Accidental Release Measures

6.1 Personal precautions, protective equipment and emergency procedures

Avoid inhalation and contact with skin and eyes. A self-contained breathing apparatus is recommended in case of a major spill.

6.2 Environmental precautions

Keep away from drains, soil, and surface and groundwater.

6.3 Methods and materials for containment and cleaning up

Clean up spillage promptly. Remove ignition sources. Provide adequate ventilation. Avoid excessive inhalation of vapors. Gross spillages should be contained by use of sand or inert powder and disposed of according to the local regulations.

6.4 Reference to other sections

Not Applicable

7. Handling and Storage

7.1 Precautions for safe handling

Apply according to good manufacturing and industrial hygiene practices with proper ventilation. Do not drink, eat or smoke while handling. Respect good personal hygiene.

7.2 Conditions for safe storage, including any incompatibilities

Store in a cool, dry and ventilated area away from heat sources and protected from light in tightly closed original container. Avoid plastic and uncoated metal container. Keep air contact to a minimum.

7.3 Specific end use

No information available

8. Exposure Controls/Personal Protection

8.1 Control parameters

Exposure Limits: Contains no substances with occupational exposure limit values

Engineering Controls: Use local exhaust as needed.

8.2 Exposure controls - Personal protective equipment

Eye protection: Tightly sealed goggles, face shield, or safety glasses with brow guards and side shields, etc. as may be appropriate for the exposure

Respiratory protection: Avoid excessive inhalation of concentrated vapors. Apply local ventilation where appropriate.

Skin protection: Avoid Skin contact. Use chemically resistant gloves as needed.

9. Physical and Chemical Properties

9.1 Information on basic physical and chemical properties

Appearance: Conforms to Standard

Odor: Conforms to Standard

Color: Yellow

Viscosity: Solid

Freezing Point: Not determined

Boiling Point: Not determined

Melting Point: Not determined

Flashpoint: 157 F (69.44 C)

Auto flammability: Not determined

Explosive Properties: None Expected

Oxidizing properties: None Expected

Vapor Pressure (mmHg@20 C): 0.6437

%VOC: 44.564

Specific Gravity @ 25 C: N/A

Density @ 25 C: Not determined

Refractive Index @ 20 C: N/A

Soluble in: Oil

10. Stability and Reactivity

10.1 Reactivity None

10.2 Chemical stability Stable

10.3 Possibility of hazardous reactions None known

10.4 Conditions to avoid None known

10.5 Incompatible materials Strong oxidizing agents, strong acids, and alkalis

10.6 Hazardous decomposition products None known

11. Toxicological Information

11.1 Toxicological Effects

Acute Toxicity Estimates (ATEs) based on the individual Ingredient Toxicity Data utilizing the "Additivity Formula"

Acute toxicity - Oral - (Rat) mg/kg	(LD50: 5,234.55) Not classified - the classification criteria are not met
Acute toxicity - Dermal - (Rabbit) mg/kg	(LD50: 2,451.97) May be harmful in contact with skin
Acute toxicity - Inhalation - (Rat) mg/L/4hr	(LC50: 23.61) May be harmful if inhaled
Skin corrosion / irritation	Not classified - the classification criteria are not met
Serious eye damage / irritation	Causes serious eye irritation
Respiratory sensitization	Not classified - the classification criteria are not met
Skin sensitization	May cause an allergic skin reaction
Germ cell mutagenicity	Not classified - the classification criteria are not met
Carcinogenicity	Not classified - the classification criteria are not met
Reproductive toxicity	Not classified - the classification criteria are not met
Specific target organ toxicity-single exposure	Not classified - the classification criteria are not met
Specific target organ toxicity-repeated exposure	Not classified - the classification criteria are not met
Aspiration hazard	Not classified - the classification criteria are not met

12. Ecological Information

12.1 Toxicity

Acute aquatic toxicity	Not classified - the classification criteria are not met
Chronic aquatic toxicity	Harmful to aquatic life with long lasting effects
Toxicity Data on soil	No data available
Toxicity on other organisms	No data available

12.2 Persistence and degradability No data available

12.3 Bio-accumulative potential No data available

12.4 Mobility in soil No data available

12.5 Other adverse effects No data available

13. Disposal Conditions

13.1 Waste treatment methods

Do not allow product to reach sewage systems. Dispose of in accordance with all local and national regulations. Send to a licensed waste management company. The product should not be allowed to enter drains, water courses or the soil. Do not contaminate ponds, waterways or ditches with chemical or used container.

14. Transport Information

Regulator	Class	Pack Group	Sub Risk	UN-nr.
U.S. DOT (Non-Bulk) Chemicals NOI	Not Regulated - Not Dangerous Goods			
ADR/RID (International Road/Rail) Chemicals NOI	Not Regulated - Not Dangerous Goods			
IATA (Air Cargo) Chemicals NOI	Not Regulated - Not Dangerous Goods			
IMDG (Sea) Chemicals NOI	Not Regulated - Not Dangerous Goods			

15. Regulatory Information**Additional European Regulations:**

European Union (EINECS, ELINCS or NLP): 100.00% (by Wt) of the components are listed or exempt.

Additional Asian Regulations:

Australian AICS: 99.98% (by Wt) of the ingredients on AICS or notified.

Chinese IECS: 99.98% (by Wt) of the ingredients on IECS.

Japan ENCS: 99.98% (by Wt) of the ingredients on ENCS, fall within the 1000 kilogram per annum exemption or have been notified.

Korea KECL: 99.98% (by Wt) of the ingredients on KECL, fall within the 100 kilogram per annum exemption or have been notified.

New Zealand NZIoC: 63.59% (by Wt) of the ingredients on NZIoC.

Philippines PICCS: 99.98% (by Wt) of the ingredients on PICCS.

The Status of the following ingredient(s) is NOT known for the registration lists noted;**Lists noted within <> brackets after name**

FC&F#D-879	0.01 - 0.1%	Yellow Liquid Dye #D-879 (French Color & Fragrance Co. Compound) : < AICS, KECL, NZIoC>
90622-46-1 292-448-0	30 - 40 %	Alkanes, C14-C16 : < NZIoC>

16. Other Information

GHS H-Statements referred to under section 3

Total Fractional Values

(TFV) Risk

(2.76) Sensitization, Skin, Category 1B

(4.03) Aquatic Chronic Toxicity, Category 3

(TFV) Risk

(1.37) Eye Damage/Eye Irritation, Category 2A

Department issuing data sheet: Operations / Compliance Group

Department E-mail address: www.rubbermaidcommercial.com

General Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of Safety Data Sheet