

# PRODUCT DATA SHEET



**Model: DB100C**  
**6" to 8" Corded Inductor In-Line Duct Fan**  
250 Max Boosted CFM, 160 Free Air CFM  
30 Running Watts, 0.35 Amps, 120 VAC, 60 Hz  
UL® Listed  
1 Year Limited Warranty  
6" to 8" Diameter  
Assembled in the USA  
Primary UOM: EA  
Shipping Multiple: 6

## Performance

Max Boosted CFM	Free Air CFM	Watts	Amps	Volts	Hz	dBA	Sones
250	160	30	0.35	120	60	50	2.2

## Hazardous Material Info

Not Applicable

## Customs Tariff Classification

HS Code	Country of Origin	NAFTA Preference Criterion	NAFTA Producer Index
8414596090	USA	B	Y

## Packaging Metrics

	UPC/SCC	Width (in)	Height (in)	Depth (in)	Weight (lbs)
Unit	066028000705	6.25	6.25	6.25	
Master Case	40066028000703				