



VKM36

36" Versa-Kool Mobile Spot Cooler Fan



Air Velocity (@ 5 times diameter) :	810	Guard Spacing (inches) :	1/2 - 1 UL507
BESS Lab Performance Test No. :	13213	Housing Color :	White
Blade Color :	Gray	Housing Material :	Polyethylene
Blade Material :	Galvanized Steel	Max RPM :	825
CFM (free air) :	11700	Nameplate Amps :	7/3.5
CFM Calculation Standard :	ANSI/AMCA Standard 230-99	Number of Wings :	3
CFM Range (Free Air) :	10001 - 15000	Oscillating :	No
CFM/Watt (free Air) :	26.5	Phase :	1
Component Certifications :	Motor - UL/CSA	Power (hp) :	1/2
Cord :	Included - Wired	Power (Voltage & Phase) :	115/230 Single Phase
Cord Length (feet) :	7	Product Color :	White
Country of Origin :	US	Product Weight (pounds) :	85
Diameter (inches) :	36	Speed Control Compatible :	No
Drive Type :	Direct	Speeds :	1
Fixed or Portable :	Portable	Switch :	On cord
Frequency (Hz) :	60	VFD Compatible :	No
Guard Color :	White	Voltage :	115/230
Guard Material & Coating :	Powder Coated Steel		

