

The Wiseway Non-Electric Pellet Stove



Tradition, Quality, and Value Since 1869



Heats up to 2,400 Sq. Ft.
78% Efficiency Rating
1.9 Grams per Hour
60 lb. Hopper Capacity
34 Hour Burn Time
No Blower or Auger Noise

Depth: 15 inches
Width: 24 inches
Height: 52 inches
UL Approved
EPA Certified
Mobile Home Approved



Introducing the Wiseway Pellet Stove, a new way to heat your home. This stove has taken the wood stove's natural draft and incorporated the use of manufactured fuel to give you a precise measured heat value and a continuous burner feed system. The Wiseway Pellet Stove heats your home with zero electricity by utilizing a natural gravity feed system giving you an affordable alternative heating system. It features a silent operation: absolutely no blower or operation noise. Don't wait for a power outage, be safe and comfortable with this non-electric patented pellet stove.




**Easy Viewable
Window**



Adjustable Damper



Easy Cleanup



Thermostat