



model EVAP40



evaporative vortex humidifier  
Humidifies all the air more effectively.™



<b>Model</b>	<b>EVAP40</b>
Item Number	HU1-0045-65BB
Color	Cool Gray
Unit UPC	0 43765 00940 6
SCC 14	100 43765 00940 3
Country of Origin	USA
Warranty	5 years
Speeds	Low / Med / High
Humidity Settings	Min - Max
Watts	43
Unit Dimensions	19.50" L x 10.50" W x 13.50" H
Carton Dimensions	20.19" L x 11.44" W x 13.25" H
Carton Weight	10 lbs
Carton Cube	1.77
Case Dimensions	41.25" L x 12.00" W x 14.25" H
Case Weight	21 lbs
Case Quantity	2
Case Cube	4.08
40" x 48" GMA Pallet Qty.	40
48' Truck Load Qty.	1,120
53' Truck Load Qty.	1,200



**Vornado Vortex Humidification**



**Automatic Humidity Control and 3 Fan Settings**



**4 Gallon Capacity, 4 Gallon Output (Over 24 Hours)**



**Coverage up to 1,000 sq.ft.**



**Whisper Quiet**

**Suggested Ad Copy**

The EVAP40 Evaporative Vortex Humidifier creates a comfortable, perfectly humidified living space quickly and quietly. Vornado's deep pitched blades pull large volumes of harsh, dry air through the unit, and then, using Vornado's signature Vortex Action, circulates the humidified air throughout the room, providing complete and uniform humidification in spaces up to 1,000 sq. ft. The EVAP40 delivers automatic humidity control with a built-in humidistat. An easy-to-use control panel allows you to choose your desired humidity level and fan speed (low, medium, or high). Its extra-large 4 gallon capacity provides 4 gallon output every 24 hours when operated continuously on high, allowing for long, uninterrupted operation and fewer refills. Includes two durable water tanks that are easy-to-fill, spill-proof & leak-free. 5 year limited warranty.

Designed, engineered and assembled in U.S.A.  
This product has earned the ETL Listing mark.  
©2015 Vornado Air, LLC.  
Andover, Kansas 67002 U.S.A  
Specifications subject to change without notice.



**5 Year Limited Warranty**

**1.800.234.0604  
www.vornado.com**