



fitted with

- work equipment**
- connected load**
- power consumption**
- glare-free**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- material**
- surface**
- colour**
- weight (net)**
- mains lead**
- design**
- fastening**
- dimension**
- special features**

- 36 x Light-emitting diode
- light colour neutral white, 3800-4300 K, Color Rendering Index (CRI)=80
- electronic transformer
- 100-240 V; 50/60 Hz
- approx. 47 W
- conical prismatic screen
- IP 20
- II
- continuously dimmable
- press switch
- sectional aluminium
- anodised
- aluminium coloured anodised
- approx. 1.8 kg
- approx. 6,3 m; mains plug
- CEE 7/XVI
- mounted version
- screw-down bracket; horizontal
- 658
- fixed connection




CEE 7/XVI

illuminance

measuring conditions: d=50cm

Em: 1641 lx
Emax: 4046 lx
Emin: 329 lx



luminous intensity

