



Product Specifications

Catalog number	EC42DD
EDP number	60145
Description	42-inch Variable Speed EC motor Mancooler
Nominal diameter	42-inch blade diameter
Performance	15250 CFM at maximum speed
Max Temperature operating	110 degrees F
Speed	Variable; 466 RPM max to 46 minimum (approx.)
Sound	75 dBA @ maximum speed to 25 dBA @ minimum
Voltage	115 volts 1 phase 60 hertz
Amps	4.2 amps
Watts	591 watts
Power	1 HP nominal
Motor Enclosure	IP56 in a TEAO application
Electric Cord	10-foot SJT 3 conductor
Fan enclosure	Steel
Finish	Hammertone Black on Grey
Unit support	(2) Rubber wheels plus (2) Swivel Casters
Weight (package)	66 pounds
Package size	51" (L) x 27" (W) x 53" (H)
Guards	OSHA compliant

