

# Amana® Commercial

Project #: \_\_\_\_\_

Item #: \_\_\_\_\_

## Medium Volume

### Amana Commercial Microwave Model RCS10DSE



Model RCS10DSE shown

#### Medium Volume

This category of microwave is ideal for...

##### Applications:

- Coffee shops
- Ethnic restaurants
- Concessions
- Dessert stations

All ACP, Inc. commercial ovens are backed by our Culinary Center. Call us with any question regarding food preparation, menu development and cooking times. 866-426-2621.



#### Power Output

- 1000 watts of power.
- Four power levels.

#### Easy to Use

- User friendly ten minute dial timer lights up for at-a-glance monitoring.
- Timer automatically resets to zero if door is opened during heating. User option allows manual reset to zero.
- See-through door and lighted interior for monitoring without opening the door.
- 1.2 cubic ft. (34 liter) capacity accommodates a 14" (356 mm) platter, prepackaged foods and single servings.
- Stackable to save valuable counter space.

#### Easy to Maintain

- Stainless steel exterior and interior for easy cleaning and a commercial look.
- Constructed to withstand the foodservice environment.
- Non-removable air filter protects oven components.
- Backed by the ACP, Inc. 24/7 ComServ Support Center, 866-426-2621.
- ETL Listed.



AIA File #:

Specification #:

Part No. 20154712  
Updated 8/8/14  
Original Instructions



© 2014 ACP, Inc.  
Cedar Rapids, Iowa 52404

225 49th Ave Dr. SW Cedar Rapids, IA 52404  
®/™ © 2012 Amana. All rights reserved. Brand used under license.


800-233-2366

319-368-8120

Fax: 319-368-8198

www.acpsolutions.com

# Amana Commercial Microwave Model RCS10DSE | Medium Volume



Installation clearance: 2" all sides

Drawings available from KCL CADlog - techs@kclcad.com

Specification #:

| Specifications            |                                |                       |             |
|---------------------------|--------------------------------|-----------------------|-------------|
| Model                     | RCS10DSE                       | UPC Code 728028129465 |             |
| Configuration             | Countertop                     |                       |             |
| Control System            | Dial                           |                       |             |
| Max. Cooking Time         | 10:00                          |                       |             |
| Power Levels              | 4                              |                       |             |
| Time Entry Option         | Yes                            |                       |             |
| Microwave Distribution    | Rotating antenna, top          |                       |             |
| Magnetron                 | 1                              |                       |             |
| Stackable                 | Yes                            |                       |             |
| Stage Cooking             | 1                              |                       |             |
| Interior Light            | Yes                            |                       |             |
| Door Handle               | Grab & Go                      |                       |             |
| Signal                    | End of cycle                   |                       |             |
| Exterior Dimensions       | H 13 7/8" (352)                | W 22" (559)           | D*19" (483) |
| Cavity Dimensions         | H 8 1/2" (216)                 | W 14 1/2" (368)       | D 15" (381) |
| Door Depth                | 32 3/4" (832), 90°+ door open  |                       |             |
| Usable Cavity Space       | 1.2 cubic ft. (34 liter)       |                       |             |
| Exterior Finish           | Stainless steel                |                       |             |
| Interior Finish           | Stainless steel                |                       |             |
| Power Consumption         | 1550 W, 13 A                   |                       |             |
| Power Output**            | 1000 W** Microwave             |                       |             |
| Power Source              | 120V, 60 Hz, 15 A single phase |                       |             |
| Plug Configuration / Cord | NEMA 5-15                      | 5 ft. (1.5m)          |             |
| Frequency                 | 2450 MHz                       |                       |             |
| Product Weight            | 41 lbs. (19 kg.)               |                       |             |
| Ship weight (approx.)     | 48 lbs. (22 kg.)               |                       |             |
| Shipping Carton Size      | H 17" (432)                    | W 26" (660)           | D 20" (508) |
| UPS Shippable             | Yes                            |                       |             |

AIA File #:

Measurements in ( ) are millimeters

\* Includes handle

\*\* IEC 60705 Tested

## Specifications

Commercial microwave shall have a user-friendly 10 minute dial timer with illuminated digits and an end of cycle audible signal. Timer shall automatically reset if the door is opened during heating with user option to manually reset to zero. There shall be a four power level and cooking stage. Microwave output shall be 1000 watts distributed by one magnetron with a rotating top antenna to provide superior even heating throughout the cavity. Durable door shall have a tempered glass window and a grab and go handle with a 90°+ opening for easy access. An interior light shall facilitate monitoring without opening the door. The large 1.2 cubic ft. (34 liter) cavity shall accommodate a 14" (356 mm) platter. Interior ceramic shelf shall be sealed and recessed on oven bottom to reduce plate-to-shelf edge impact. Oven shall have a stainless steel exterior and interior and be stackable to save counter and shelf space. The air filter shall be permanently affixed to the front of the oven. Microwave oven shall comply with standards set by the U.S Department of Health and Human Services, UL923 for safety and NSF4 for sanitation.



## Warranty

Warranty Certificate for this product can be found on the ACP, Inc. website at:

[www.acpsolutions.com/warranty](http://www.acpsolutions.com/warranty)



## Service

All products are backed by the ACP, Inc. 24/7 ComServ

