



Overview

Model Name	APC Back-UPS BE600M1, 600VA, 120V, 1 USB charging port
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Cayman Islands , Colombia , Dominican Republic , Falkland Islands (Malvinas) , Guyana , Haiti , Jamaica , Netherlands Antilles , Puerto Rico , Trinidad And Tobago , United States , VIRGIN ISLANDS (UNITED STATES)

Output

Output Power Capacity	330 Watts / 600 VA
Max Configurable Power (Watts)	330 Watts / 600 VA
Nominal Output Voltage	120V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Standby
Waveform Type	Stepped approximation to a sine wave
Output Connections	(2) NEMA 5-15R (Surge Protection) , (5) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	5 feet (1.52 meters)
Input voltage range for main operations	92 - 139 V
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	10 hour(s)

Replacement Battery	APCRBC154
RBC Quantity	0

Communications & Management

Interface Port(s)	USB
Available SmartSlot™ Interface Quantity	0
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	490 Joules
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: instantaneous

Physical

Maximum Height	5.47 inches (139.0 mm)
Maximum Width	10.79 inches (274.0 mm)
Maximum Depth	4.13 inches (105.0 mm)
Rack Height	0 U
Net Weight	7.7 lbs (3.49 kg)
Shipping Weight	8.4 lbs (3.81 kg)
Shipping Height	7.7 inches (196.0 mm)
Shipping Width	14.29 inches (363.0 mm)
Shipping Depth	6.61 inches (168.0 mm)
Master Carton Units	2.0
Master Carton Weight	8.4 kg
SCC Codes	1073130432511 3
Units per Pallet	60.0
Pallet Weight	504.86 lbs (229.0 kg)

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 90 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	35.000 dB
Online Thermal Dissipation	16.000 BTU/hr

Conformance

Approvals	California (CEC) Battery Charger , ENERGY STAR V1.0 (USA) , FCC Part 15 Class B , NOM , UL 1778 , cTUVus
Standard warranty	3 years repair or replace
Equipment protection policy	Lifetime : \$75000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs