

## SmartRack 8U/12U/22U Expandable Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open Frame Rack

MODEL NUMBER: **SRWO8U22**



### Description

The SRWO8U22 SmartRack 8U/12U/22U Expandable Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open-Frame Rack stores and organizes EIA-standard 19-inch rack equipment compatible with 2-post mounting in network wiring closets, back offices and other secure IT areas with limited floor space where a locked enclosure is not required. Mounted to the wall or resting on the floor, this rack offers fast, easy access to network components and cabling.

Constructed from heavy-duty steel with a durable black powder-coated finish, the rack has a maximum load capacity of 150 pounds. The expandable design allows you to assemble the rack in an 8U, 12U or 22U configuration to meet your current needs, while leaving rack space in reserve for future expansion.

The rack is simple to assemble and mount to the wall. Threaded 12-24 mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails accommodate equipment up to 18 inches deep, such as network switches and patch panels. Assembly and equipment-mounting hardware is included.

### Features

#### Saves Valuable Workspace

- Perfect for network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required
- Stores and organizes EIA-standard 19 in. rack equipment compatible with 2-post mounting
- Maximum load capacity of 150 lb.

#### Expandable 2-Post Open Frame Design

- Assembles in 8U, 12U or 22U configuration to meet current needs
- Expands to add equipment later without having to buy a bigger rack
- Allows easy access for installing, configuring and servicing equipment and cabling

#### Easy Assembly and Installation

### Highlights

- Maximum load capacity of 150 lb.
- Configures to 8U, 12U or 22U of rack space
- Allows easy access to equipment and cabling
- Stores 19 in. rack equipment up to 18 in. deep
- Simple to assemble and mount

### Package Includes

- (24) 12-24 equipment mounting screws
- (8) M6 x 12 Phillips-head screws
- (16) M5 x 10 Phillips-head screws
- (2) Short vertical mounting rails
- (2) Long vertical mounting rails
- (2) Mounting rail tie plates
- (2) Top/bottom panel frames
- (2) Support straps
- (8) Zip ties
- 3 mm hex key
- Owner's manual



- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails accommodate equipment up to 18 in. deep, such as network switches and patch panels
- Rails support threaded-hole equipment mounting
- Rack spaces numbered for easy reference
- Includes assembly and equipment-mounting hardware

## Specifications

PHYSICAL	
Rack Height (U Spaces)	22
Maximum Device Depth (in.)	18.24
Maximum Device Depth (cm)	46.33
Shipping Dimensions (hwd / in.)	3.7 x 22.8 x 21.8
Shipping Dimensions (hwd / cm)	9.4 x 57.92 x 55.38
Shipping Weight (lbs.)	18.6
Shipping Weight (kg)	8.37
Unit Dimensions (hwd / in.)	17.8 (8U) , 24.8 (12U), 42.3 (22U) x 20.11 x 18.24
Unit Dimensions (hwd / cm)	45.22 (8U), 63 (12U), 107.45 (22U) x 51.08 x 46.33
Color	Black
Unit Weight Details	Weight varies depending on configuration 8U = 11.21lbs, 12U = 12.23lbs, 22U = 15.03lbs
Maximum Weight Capacity (lbs.)	150
Maximum Weight Capacity (kg)	68
Maximum Device Depth (mm)	463
CERTIFICATIONS	
Approvals	EIA-310-D, IEC 60297-3-100, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>