



COMPARE TO
 Hoyer/Joerns® C-HCA
 Invacare® 9805

13023 - Sling
 Sold Separately



COMPARE TO
 Invacare® RPL450-1
 Graham Field® LF1040

Sling Sold Separately

Hydraulic Deluxe Chrome-Plated Patient Lift with 6-Point Cradle

Item #	Product Description	For Use With	UOM
13023			1/cs
13023CSET	3" Casters, Contains Two 3" Non-Locking Caster and Two 3" Locking Caster	Low Bed	4/bx

- Chrome-plated steel provides maximum strength.
- Safely raises or lowers individuals from any stationary position.
- 6 point Swivel Bar that can accommodate, 2 or 4 sling straps, plus 2 chain connections .
- High-performance hydraulics raise or lower individuals gradually and safely.
- Easy-to-operate caster brakes provide security.
- Includes sling chains.

specifications

Boom Height	17.5" - 62"
Base Width	22.5" - 42"
Base Height	6"
Casters	5"
Weight	72 lbs.
Carton Shipping Weight	81 lbs.
Weight Limit	450 lbs.
Warranty	Limited Lifetime (frame), 1 Year Limited (pump)

Battery-Powered Patient Lift with 6-Point Cradle

Item #	UOM
13240	1/cs

- Heavy-gauge construction.
- Jumbo actuator pump with emergency button can switch to manual mode to lower patient down safely.
- Fast, easy charge from AC outlet.
- To charge, simply plug in unit. Battery does not need to be removed to be charged. Lift will not operate while plugged in. For home-care use.
- Audible warning when battery power falls below 50%.

specifications

Boom Height	27.5" - 76"
Base Width	41" (open) 24" (closed)
Base Height	4.75"
Base Clearance	2"
Casters	5" Rear
Weight	108 lbs.
Carton Shipping Weight	122 lbs.
Weight Limit	450 lbs.
Warranty	Limited Lifetime

replacement parts

13240C	Charger for 13240	1/ea
--------	-------------------	------