



COMPARE TO
 Invacare® 9805P
 Graham Field® LF1031

13023SV - Sling
 Sold Separately



Sling Sold Separately

Hydraulic, Deluxe Silver Vein Patient Lift with 4-Point Cradle

Item #	Product Description	For Use With	UOM
13023SV	5" Casters		1/cs
13023CSET	3" Casters, Contains Two 3" Non-Locking Caster and Two 3" Locking Caster	Low Bed	4/bx
13023SVLB	3" Casters	Low Bed	1/ea

- Silver Vein steel construction.
- 6 point Swivel Bar taht can accommodate 2 or 4 sling straps plus 2 chain connections.
- High-performance hydraulics raise or lower individuals gradually and safely from any stationary position.
- Choose either 3" or 5" casters.
- Adjustable-width base.

specifications	
Boom Height	17.5" - 72" (13023SV) 16.5" - 71" (13023SVLB)
Base Width	42"(open) / 22.5" (closed)
Base Height	6.5" (13023SV) 5.5" (13023SVLB)
Casters	5" (13023SV) 3" (13023SVLB)
Weight	72 lbs.
Carton Shipping Weight	84 lbs.
Weight Limit	450 lbs.
Warranty	Limited Lifetime (frame), 1 Year Limited (pump)

Low Hydraulic, Deluxe Silver Vein Kit

Item #	Product Description	UOM
13023SVKIT	Includes 13023SV Patient Lift and 13023CSET 3" Caster Set	1/cs
13023SV-6PT	Lift with 6-Point Cradle	1/cs

- Silver Vein steel construction provides maximum strength.
- 6 point Swivel Bar that can accommodate, 2 or 4 sling straps, plus 2 chain connections.
- Safely raises or lowers individuals from any stationary position.
- High-performance hydraulics raise or lower individuals gradually and safely.
- Comes standard with 5" casters.
- Easy-to-operate caster brakes provide additional security.
- Adjustable-width base.

specifications	
Boom Height	17.5" - 72"
Base Width	42" (open) 22.5" (closed)
Base Height	6.5"
Casters	5"
Weight	72 lbs.
Carton Shipping Weight	84 lbs.
Weight Limit	450 lbs.
Warranty	Limited Lifetime (frame), 1 Year Limited (pump)