



Chrome Sport Wheelchair

Dual axle

HCPCS: K0001 / K0002 / K0007



INSET A

- Carbon steel frame with chrome coating provides an attractive, chip-proof, easy-to-maintain finish (Figure A)
- Embossed vinyl upholstery is durable, lightweight, attractive and easy-to-clean
- Urethane tires mounted on composite wheels provide durability and low maintenance
- 8" front casters, adjustable in three positions
- Padded armrests provide additional comfort
- Carry pocket on backrest provides additional convenience
- Comes with swing-away footrests or elevating leg rests with tool-free adjustable length riggings
- Plastic foot plates
- Comes with push-to-lock wheel locks

PRODUCTS	Description
CS16DDA-SF	ChromeSport W/C 16Det. Desk SF, 1/cs
CS16DDA-ELR	ChromeSport W/C 16Det. Desk ELR, 1/cs
CS18DDA-SF	Chrome Sport W/C 18 DET.DESK, 1/cs
CS18DDA-ELR	Chrome Sport W/C 18 DET. DESK ELR, 1/cs
CS20DDA-SF	ChromeSport W/C 20in Det. Desk SF, 1/cs
CS20DDA-ELR	ChromeSport W/C 20Det. Desk ELR, 1/cs
CS20DFA-SF	ChromeSport W/C 20Det.FullArm SF, 1/cs
CS20DFA-ELR	ChromeSport W/C 20Det.FullArm ELR, 1/cs

SPECIFICATIONS	Description
Width Open with 16" Seat	24"
Width Open with 18" Seat	26"
Width Open with 20" Seat	28"
Width Closed	12.5"
Height	36"
Seat-To-Floor Height	17.5" - 19.5"
Back Height	16"
Seat Depth	16"
Length with Rigging	42"
Product Weight with 16" Seat	39 lbs.
Product Weight with 18" Seat	40 lbs.
Product Weight with 20" Seat	41 lbs.
Carton Shipping Weight with 16" Seat	45 lbs.
Carton Shipping Weight with 18" Seat	46 lbs.
Carton Shipping Weight with 20" Seat	47 lbs.
Weight Limit with 16" Seat	250 lbs.
Weight Limit with 18" Seat	300 lbs.

SPECIFICATIONS

Description

Weight Limit with 20" Seat

350 lbs.

Warranty

Limited 3 Year

ACCESSORIES

Description

STDS806

Anti-Fold Bar, 1/ea

STDS833N

Anti-Tippers With Wheels Black, 1/pr

STDS818

Anti-Tippers without Wheels, Chrome, 1/pr

STDS831

Heel Loops, 1/bx

WASR

Limb Support, Right, 1/ea

WASL

Limb Support, Left, 1/ea

STDS834

Overhead Anti-Theft Device Single Pole, 1/ea

STDS850

Seat Belts, Auto-Clasp Type Closure, 1/ea

STDS851

Seat Belts, Hook and Loop Fastener Type Closure, 1/ea

STDS855

Seat Belts, Auto-Clasp Type Closure, Bariatric, 1/ea

STDS856

Seat Belts, Hook and Loop Fastener Type Closure, Bariatric, 1/ea

STDS820

Telescoping IV Pole Attachment, 1/ea

STDS801GT

Wheel Lock Extension, 1/ea

STDS1034

Wheelchair Cane/Crutch Holder, 1/ea

PARTS

Description

STDS806

Anti-Fold Bar, 1/ea

STDS833N

Anti-Tippers With Wheels Black, 1/pr

STDS818

Anti-Tippers without Wheels, Chrome, 1/pr

STDS836

Chart Carry Pocket, 1/ea

STDS831

Heel Loops, 1/bx

WASR

Limb Support, Right, 1/ea

WASL

Limb Support, Left, 1/ea

STDS823

Overhead Anti-Theft Device, 1/ea

STDS834

Overhead Anti-Theft Device Single Pole, 1/ea

STDS850

Seat Belts, Auto-Clasp Type Closure, 1/ea

STDS851

Seat Belts, Hook and Loop Fastener Type Closure, 1/ea

STDS855

Seat Belts, Auto-Clasp Type Closure, Bariatric, 1/ea

STDS856

Seat Belts, Hook and Loop Fastener Type Closure, Bariatric, 1/ea

STDS820

Telescoping IV Pole Attachment, 1/ea

STDS803

Universal Oxygen "E" Cylinder Holder, 1/ea

STDS804

Universal Oxygen "E" Cylinder Holder with IV Pole Attachment, 1/ea

STDS801GT

Wheel Lock Extension, 1/ea

STDS1034

Wheelchair Cane/Crutch Holder, 1/ea