






### 3-Position Recliner

Item #	Color	UOM
D574-BR	Blue Ridge 	1/cs
D574-J	Jade 	1/cs
D574-R	Rosewood 	1/cs

- 3-positions: upright (Figure A), deep recline and elevated leg rest/footrest. (Figure B)
- Retractable lock bar secures the chair in the desired position.
- Self-adjusting suspension in the seat prevents bottoming out.
- Side panels “pop off” for easy cleaning and maintenance.
- Large, blow-molded tray locks in 5 positions and can be stored on the side of the chair.
- 5" casters (2 with locks) make it easy to move and secure the recliner.
- Wide, comfortable armrests are angled to provide support in any reclined position.
- Neutral-colored, sturdy steel frame is easy to clean and maintain.
- Moisture barrier on seat prevents seepage.
- Comfortable built-in headrest. Foam and vinyl meet California Technical Bulletin 117 Standard.

specifications	
Overall Dimensions	47" (H) X 25" (W) X 41" (D)
Width	20" between arms
Seat to Floor Arm Height	9" - 26"
Seat Dimensions	21" (H) x 19" (W) x 19" (D)
Carton Shipping Weight	110 lbs.
Weight Limit	250 lbs.
Warranty	Limited Lifetime on Frame, 1 Year on Upholstery and Moving Parts