



Stand-Assist Lift

Item #	UOM
13246	1/cs

- Provides stable assistance in standing, transferring and toileting.
- Four sling attachment points enable the lift to accommodate a variety of stand-up sling designs.
- Extra-wide, non-skid foot plate provides a stable base for foot positioning (Figure A).
- Soft, padded adjustable leg support includes a support strap to secure legs to the support. (Figure A)
- Easy-roll 4" casters mean stability and easy maneuverability over a variety of surfaces. (Figure B)
- 4.5" under-bed clearance provides access under most long term care beds.

- 24V DC motor provides power and reliability.
- Motor has an emergency stop button and manual lowering feature.
- Fast charging, rechargeable battery is removable to eliminate lift downtime.
- Battery has a charged and low-charge indicator. Audible tone when charge is complete.
- Battery charge meter indicates the battery power status while in use. Audible tone when battery power is below 50%.
- Includes removable, rechargeable battery item #13240BATT (Figure C), charging station #13255 (Figure D) and wall-mount bracket item #13260 (Figure E).

specifications

Boom Height	26" - 81"
Base Width	40" (Open) 24.5" (Closed)
Base Clearance	4.5"
Casters	3" (Front) 4" (Rear)
Weight	113 lbs.
Carton Shipping Weight	128 lbs.
Weight Limit	400 lbs.

replacement parts

13255	External Charger	1/ea
13240BATT	Rechargeable Battery	1/ea
13260	Wall-Mounted Bracket	1/ea