



Engineered for comfort, protection and style, Genesis is the number one selling premium eyewear in the market, delivering an incredible range of superior product benefits. Built with MMT— Multi-Material Technology® and a high level of adjustability, Genesis provides workers with extraordinary all-day comfort and raises the bar on compliance.



SAFETY EYEWEAR

Genesis®



UVEX™

by Honeywell

Genesis®

High Performance Protection

- Wrap-around 9-base uni-lens style for uncompromised peripheral vision and superior coverage.
- Available with Dura-streme™ dual coating technology which combines our two best lens coatings — Uvextreme® anti-fog on the interior and Ultra-dura® anti-scratch on the exterior — for 3x longer lens life.*
- Offers highest available impact protection. Meets ANSI Z87.1-2003 (High Impact) and military V₀ ballistic impact test (protection against impact energies 7x higher than ANSI requirements).
- Certified to meet CSA Z94.3 standards.
- Available in a wide range of lens tints to address the needs of virtually any work environment.

Superior Comfort & Fit

- Soft elastomer browguard diffuses and deflects impact while providing comfort at all contact points.
- Soft flexible fingers on the nose piece adjust and conform to almost any nasal profile to reduce slippage.
- Adjustable temple length and lens inclination for a customizable fit.

Product Platform Advantages & Value

- Economical and easy lens replacement system allows for multiple lens tints and extends the life of the eyewear.
- Multiple models in a family offers standardization while offering workers choice.
- Lifetime frame guarantee.



Three position ratchet lens inclination adjusts to complete the fitting system and provides unsurpassed extended wear comfort.



Soft, flexible nose fingers conform to fit a variety of nasal profiles.



A unique ventilation channel, between the frame and lens, vents the eye socket area to deliver an outstanding level of moisture and fog control.



Adjustable temple length enables wearers to custom fit the eyewear to their facial profile.



*Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application.

Genesis®

All Uvex® lenses offer 99.9% ultra-violet protection.

SAFETY EYEWEAR



Clear — Ideal for most indoor work applications



Espresso — Minimizes strong outdoor sunlight and glare



Amber — For low-light applications where enhanced contrast is needed



SCT-Vermilion — For indoor applications where contrast is needed, such as inspection



SCT-Blue — For applications with high levels of sodium vapor lighting



Gold Mirror — Deflects sunlight and glare



SCT-Reflect 50 — Light mirror coating for varying light conditions



SCT-Gray — Minimizes outdoor glare and offers true color recognition



SCT-Low IR — When peripheral IR protection is required



Infra-dura® Welding — Available in shades 2.0, 3.0 and 5.0 for welding, brazing and cutting



50% Gray — Minimizes outdoor sunlight and glare



Dark Gray — Minimizes eye fatigue due to outdoor sunlight and glare

FOR MORE INFORMATION, CONTACT:
Sperian Protection Americas, Inc.
 900 Douglas Pike
 Smithfield, RI 02917-1874
 (800) 430-5490
www.uvex.us



ORDERING INFORMATION

EYEWEAR

ITEM #	FRAME COLOR	LENS TINT	LENS COATING	UPC CODE
S3200	Black	Clear	Ultra-dura	603390087851
S3200D	Black	Clear	Dura-streme	603390122859
S3200-ADV	Black	Clear	Ultra-dura	603390123405
S3200X	Black	Clear	Uvextreme	603390087868
S3200X-ADV	Black	Clear	Uvextreme	603390122965
S3201	Black	Espresso	Ultra-dura	603390087875
S3201X	Black	Espresso	Uvextreme	603390087882
S3202	Black	Amber	Ultra-dura	603390087899
S3202X	Black	Amber	Uvextreme	603390102837
S3203	Black	Gold Mirror	Ultra-dura	603390087905
S3204	Black	SCT-Reflect 50	Ultra-dura	603390087912
S3205X	Black	SCT-Gray	Uvextreme	603390095221
S3206	Black	Shade 2.0 Infra-dura	Ultra-dura	603390095115
S3207	Black	Shade 3.0 Infra-dura	Ultra-dura	603390095122
S3208	Black	Shade 5.0 Infra-dura	Ultra-dura	603390095139
S3209	Black	SCT-Low IR	Ultra-dura	603390095146
S3210X	Black	SCT-Vermilion	Uvextreme	603390094989
S3211X	Black	SCT-Blue	Uvextreme	603390095009
S3212X	Black	Dark Gray	Uvextreme	603390100192
S3213X	Black	50% Gray	Uvextreme	603390106927
S3220	Earth	Clear	Ultra-dura	603390088537
S3220X	Earth	Clear	Uvextreme	603390088544
S3221	Earth	Espresso	Ultra-dura	603390088551
S3221X	Earth	Espresso	Uvextreme	603390088568
S3222	Earth	Amber	Ultra-dura	603390088575
S3223	Earth	Gold Mirror	Ultra-dura	603390088582
S3224	Earth	SCT-Reflect 50	Ultra-dura	603390088599
S3240	Vapor Blue	Clear	Ultra-dura	603390088674
S3240X	Vapor Blue	Clear	Uvextreme	603390088681
S3241	Vapor Blue	Espresso	Ultra-dura	603390088698
S3241X	Vapor Blue	Espresso	Uvextreme	603390088704
S3242	Vapor Blue	Amber	Ultra-dura	603390088711
S3243	Vapor Blue	Gold Mirror	Ultra-dura	603390088728
S3244	Vapor Blue	SCT-Reflect 50	Ultra-dura	603390088735
S3260	Patriot - Red, White, Blue	Clear	Ultra-dura	603390110979
S3260X	Patriot - Red, White, Blue	Clear	Uvextreme	603390110986
S3263	Patriot - Red, White, Blue	Gold Mirror	Ultra-dura	603390111013
S3600	Mercury Red	Clear	Ultra-dura	603390122224
S3600X	Mercury Red	Clear	Uvextreme	603390122231
S3601	Mercury Red	Espresso	Ultra-dura	603390122248
S3601X	Mercury Red	Espresso	Uvextreme	603390122255
S3602	Mercury Red	Amber	Ultra-dura	603390122262
S3603	Mercury Red	Gold Mirror	Ultra-dura	603390122279
S3604	Mercury Red	SCT-Reflect 50	Ultra-dura	603390122286

REPLACEMENT LENSES

ITEM #	LENS TINT	LENS COATING	UPC CODE
S6900	Clear	Ultra-dura	603390089343
S6900D	Clear	Dura-streme	603390122927
S6900X	Clear	Uvextreme	603390089350
S6901	Espresso	Ultra-dura	603390089367
S6901X	Espresso	Uvextreme	603390089374
S6902	Amber	Ultra-dura	603390089381
S6902X	Amber	Uvextreme	603390102844
S6903	Gold Mirror	Ultra-dura	603390089398
S6904	SCT-Reflect 50	Ultra-dura	603390089404
S6905X	SCT-Gray	Uvextreme	603390095030
S6906	Shade 2.0 Infra-dura	Ultra-dura	603390095047
S6907	Shade 3.0 Infra-dura	Ultra-dura	603390095054
S6908	Shade 5.0 Infra-dura	Ultra-dura	603390095061
S6909	SCT-Low IR	Ultra-dura	603390095153
S6910X	SCT-Vermilion	Uvextreme	603390095160
S6911X	SCT-Blue	Uvextreme	603390095177
S6912X	Dark Gray	Uvextreme	603390100277
S6913X	50% Gray	Uvextreme	603390106934

Packaging Information (Eyewear):
 Ind. Box, 10 / Stocker, 200 / Master Case
 Master Case Weight: 32 pounds
 Master Case Dimensions: 29" x 15" x 24"

Packaging Information (Replacement Lenses):
 Ind. Polybag, 10/Box, 200/Master Case
 Master Case Weight: 11 pounds
 Master Case Dimensions: 18" x 13 1/4" x 10"

Uvextreme® anti-fog coating performs under the most extreme conditions and will not wear off after repeated cleanings. It is permanently bonded to the lens and retains anti-scratch, anti-static and UV protection properties. Ultra-dura® hard coat is permanently bonded to the lens and is scratch-resistant and chemical-resistant. Uvex Dura-streme™ lenses combine our two best lens coatings on one lens: Ultra-dura on the exterior and Uvextreme on the interior to provide up to 3x* more lens life.

*Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application.

